

Item code

# TAVH 06 LG32



## Product description

<b>Version</b>	HYGENIC enclosures T-TYPE /H version
<b>Series</b>	Hoods with 1 lever
<b>Product type</b>	with one lever in thermoplastic material
<b>Variant</b>	top entry
<b>Family</b>	T-TYPE insulating enclosures
<b>Size</b>	size "44.27"

## Technical data

<b>Operating temperature range (min, max)</b>	-40°C ... +70°C
<b>Material</b>	thermoplastic
<b>IP degree of protection</b>	IP66/IP69
<b>Cable entry</b>	M25

## Other technical details

<b>Weight</b>	105,50 g
---------------	----------

## Approvals / Standards

<b>Quality mark</b>	UL <sup>®</sup> (type:12), EAC
<b>Conformity</b>	CQC, CE

## General ordering information

<b>EAN code</b>	8015747149594
<b>Tariff number</b>	85369095

## Packaging Information

<b>Sub-packaging weight</b>	0,53 kg
<b>Sub-packaging description</b>	Plastic packaging
<b>Sub-packaging quantity</b>	5 Pcs
<b>Sub-packaging EAN barcode</b>	8015747149907