

419T
Hammer drill bits with milled shanks, 4 spirals and 4 cutters, SDS Plus tang

HVA~ 1650

- 4 cutters
- 4 spirals
- For drilling into walls, cement, concrete, stones

	art.	Ø mm	L mm
004190604	419T 5X110	5	110
004190606	419T 5X160	5	160
004190612	419T 6X110	6	110
004190614	419T 6X160	6	160
004190616	419T 6X210	6	210
004190628	419T 7X160	7	160
004190630	419T 8X110	8	110
004190632	419T 8X160	8	160
004190634	419T 8X210	8	210
004190636	419T 8X260	8	260
004190638	419T 8X310	8	310
004190644	419T 9X160	9	160
004190650	419T 10X160	10	160
004190652	419T 10X210	10	210
004190654	419T 10X260	10	260
004190656	419T 10X310	10	310
004190660	419T 10X460	10	460
004190664	419T 12X160	12	160
004190666	419T 12X210	12	210
004190668	419T 12X260	12	260
004190674	419T 12X460	12	460
004190686	419T 14X160	14	160
004190690	419T 14X260	14	260
004190692	419T 14X310	14	310
004190696	419T 14X460	14	460
004190712	419T 16X210	16	210
004190714	419T 16X260	16	260
004190716	419T 16X310	16	310
004190720	419T 16X460	16	460
004190724	419T 18X260	18	260
004190728	419T 20X310	20	310

