




Part Number : [5601250500](#)
Product Description : DuraClik Wire-to-Board
Independent Secondary Lock (ISL) Retainer, 5 Circuits,
Gray
Series Number : 560125
Status : Active
Product Category : Connector Accessories



Documents & Resources

Drawings

[5601250500_sd.pdf](#)
3D Models and Design Files
[5601250500_stp.zip](#)

Specifications

[AS-560123-001-001.pdf](#)
[PS-560123-001-001.pdf](#) (Tin Plating)
[PS-560123-003-001.pdf](#) (Tin Plating)
[5601240131-000.pdf](#) (Gold Plating)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Accessories
Series	560125
Description	DuraClik Wire-to-Board Independent Secondary Lock (ISL) Retainer, 5 Circuits, Gray
Application	Automotive
Component Type	Independent Secondary Lock
Product Name	DuraClik
UPC	889056791069

Physical

Circuits (Loaded)	5
Circuits (maximum)	5
Color - Resin	Gray
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	0.065/g
Number of Rows	1
Packaging Type	Bag
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +130°C

Mates With / Use With

Use with Part(s)

Description	Part Number
DuraClik ISL Wire-to-Board Receptacle Housing, Single Row, White, 5 Circuits	<u>5601230500</u>