

FEATURES

- Locking nuts for heavy-duty applications
- Glass-filled nylon inserts.
- To DIN985
- A4 grade 18/8 stainless steel (Type 316 S16)

RS PRO, M4, Plain Nylon Insert Lock Nut

RS Stock No.: 767-810



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From the trusted RS PRO brand, these lock nuts contain a nylon insert for safe and secure fastening. They are designed to remain secure despite conditions of severe vibration. The nut is made from A4 stainless steel with a bright zinc plating, for durability and environmental resistance over a long period of use. As it is A4 graded, it is even suitable for use in challenging environments.

General Specifications

Thread Size	M4
Type	Nylon Insert
Material	Stainless Steel
Finish	Plain
Grade	A4
Applications	Domestic appliances such as washers and dryers, Industrial machinery, Automotive industry

Mechanical Specifications

Stainless Steel Type	A4 316
Specification	DIN 985

Approvals

Compliance/Certifications	RoHS
----------------------------------	------



RS Stock No.	Thread Size
275692	M16
275709	M20
521917	M3
521923	M4
521939	M5
521945	M6
521951	M8
521967	M10
521973	M12
767804	M3
767810	M4
767826	M5
767832	M6
767848	M8
767854	M10
2484539	M12
521939	M5