

LEDLENSER iSEO3

The Ledlenser iSEO3 is a robust, high quality work head lamp designed for professionals who need to use a light source often. It features a premium Power LED on the front housed inside a lightweight but strong polycarbonate housing. The LEDs offers bright white or glare-free red light, as well as three interchangeable Smart Light Technology light options: Power, Low Power and Signal. On Power setting the iSEO3 will project brilliant light up to 100 metres at 100 lumens. To preserve battery life a Low Power option gives up to 40 hours burn time. The lamp head can be rotated 60 degrees, which helps reduce neck strain, and the internal reflector lens is equipped with Ledlenser's patented Advanced Focus System for efficient, even lighting all the way through from spot to flood beam. The simple twist focus allows the light to be instantly adjusted with just one hand, while a Transport Lock prevents accidental battery discharge and the head lamp from switching on accidentally when not in use. The distinctive yellow-black high-comfort headband makes the iSEO3 easy to find in the most cluttered working environment. The iSEO3 takes three AAA batteries (included) and is supplied with a pouch for protective storage.

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class- leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Battery-operated head lamp
- Premium Power LED (white light) + glare-free LED (red light)
- Advanced Focus System (AFS). Patented reflector and lens combination for intense spot (distance) or flawless flood (near) illumination
- Smart Light Technology - Power, Low Power, Signal
- Instant Focusing - focus the light with just one twist
- Transport Lock – to prevent accidental battery drain
- Lamp head swivels 60°
- Water-resistant (IPX6)
- Supplied with: Helmet Mount Kit, Pouch, Helmet Clips, 3x AAA batteries

Technical Information

iSEO3	BOOST	POWER	LOW POWER
POWER	x	100 lumens	15 lumens
BEAM DISTANCE	x	100 metres	30 metres
RUN TIME	x	10 hours	40 hours
SIZE	x	WEIGHT	105g

Supplied with: Helmet Mount Kit, Pouch, Helmet Clips, 3x AAA batteries



Code	Description	Unit Colour	Packaging	Barcode
5603	iSEO3	Black/Yellow	Box	4029113560306