


RSAO70-XL

Plummer block housing unit

Plummer block housing units RSAO, cast iron housing, radial insert ball bearing with eccentric locking collar, R seals

X-life

Technical information



Your current product variant

Material	GG	Grey cast iron
----------	----	----------------

Main Dimensions & Performance Data

d	70 mm	Bore diameter
L	360 mm	Length total
H ₂	187 mm	Height
≈m	11.94 kg	Weight

Mounting dimensions

J	282 mm	Distance fixing bore
N	27 mm	Width (slot)
N ₁	42 mm	Length (slot)

Dimensions

H	95 mm	Distance shaft axis
A	90 mm	Width (base)
A ₁	54 mm	Width (head)
H ₁	35 mm	Height (base)
B ₁	75.5 mm	Locking collar total width
S ₁	49.5 mm	Distance of raceway to locking collar
Q	M6	Connection thread for lubrication



Additional information

SAO14	Housing
GNE70-XL-KRR-B	Bearing designation

Temperature range

T _{min}	-20 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.