



Cordless MULTIMASTER AMM 700 Max AS

Battery-powered oscillating multi-tool

Our best cordless MultiTool for the most rapid work progress in interior work and renovation in the variant without battery or charger –with a bimetal saw blade for wood, metal and plastics.

Product number: 7 129 36 62 00 0

Details

- › Anti-vibration system: continuously safe and pleasant working thanks to minimal vibrations and outstanding noise insulation.
- › StarlockMax tool mounting: more work progress and greater precision thanks to 100% power transmission without losses.
- › QuickIN: tool changes in less than 3 seconds thanks to the patented tool-free FEIN rapid clamping system.
- › With the StarlockMax tool mounting, you can access around 180 FEIN accessories from the Starlock, Starlock Plus and StarlockMax performance classes.
- › 18 V FEIN PowerDrive motor: very powerful and virtually wear-free, brushless motor offering great efficiency, ability to handle extreme loads and a long service life.
- › Tacho generator: constant speeds even under load and infinitely variable electronic speed control.
- › Metal gearbox: ability to withstand high loading and outstanding service life because all the gearbox parts are made from metal.
- › Mechanical interface: for stationary operation in the table or drill jig holder or for securing the depth stop.
- › Electronic Cell Protection (ECP): ECP protects against overload, overheating and total discharge.
- › The COOLPACK technology ensures a longer battery life and therefore makes long operating periods possible.
- › The battery charge can be read off the battery.
- › Compatible with AMPShare/Bosch Professional 18 V batteries.
- › Ideally equipped for every job. Mobile working with the L-BOXX system.
- › Electronic safety cut-off – user protection should the saw blade lock, for example.

Price includes

- ✓ 1 Universal E-Cut saw blade (44 mm)
- ✓ 1 tool case (L-Boxx 136)

Product feature

- ✓ Mechanical interface

Technical data

TECHNICAL DATA

Battery voltage

18 V

Battery compatibility

Li-ion / ProCORE Li-ion

Battery interface

18 V AMPShare

Oscillations

10,000 - 19,500 rpm

Tool Holder

StarlockMax

Tool change

QuickIN

Amplitude

2 x 2,0°

Weight without storage battery

1.20 kg

Application examples

