

## FEATURES

- **Concealed design:** Provides a clean and seamless appearance for doors and panels
- **304 stainless steel construction:** Ensures durability and resistance to corrosion
- **Removable pin:** Facilitates easy installation and maintenance
- **Bolt-On/Rivet fixing method:** Offers versatile installation options
- **6.5 mm fixing hole size:** Compatible with standard hardware
- **REACH and RoHS compliant:** Meets key safety and environmental standards

## RS PRO 80 mm Concealed Hinge, 304 Stainless Steel

RS Stock No: 335-184



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price

### Product Description

This RS PRO concealed hinge is designed for applications requiring a sleek and unobtrusive hinge solution. Made from durable 304 stainless steel, it offers excellent corrosion resistance, making it ideal for both indoor and outdoor use. The hinge features a removable pin, allowing for easy installation and maintenance.

### General Specifications

Fixing Hole Size	6.5 mm
Fixing Method	Bolt-On/Rivet
Hinge Type	Concealed
Holes per Leaf	2
Pin Style	Removable Pin
Product Type	Concealed Hinge

### Mechanical Specifications

Length	80 mm
Material	304 Stainless Steel
Thickness	20 mm
Width	54.3 mm

### Approvals

Standards/Approvals	REACH, RoHS
---------------------	-------------