

ATS-XTVMEA 6 OG - Partition plate



1465362

<https://www.phoenixcontact.com/in/products/1465362>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Partition plate, depth: 46.9 mm, width: 0.8 mm, height: 104.4 mm, color: orange



Commercial data

Item number	1465362
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE2Z1X
GTIN	4063151859350
Weight per piece (including packing)	4.71 g
Weight per piece (excluding packing)	4.71 g
Country of origin	PL

ATS-XTVMEA 6 OG - Partition plate



1465362

<https://www.phoenixcontact.com/in/products/1465362>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Dimensions

Width	0.8 mm
Height	104.4 mm
Depth	46.9 mm

Material specifications

Color	orange (RAL 2003)
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

ATS-XTVMEA 6 OG - Partition plate



1465362

<https://www.phoenixcontact.com/in/products/1465362>

Classifications

ECLASS

ECLASS-11.0	27141192
ECLASS-12.0	27141192
ECLASS-13.0	27250301

ETIM

ETIM 9.0	EC004592
----------	----------

ATS-XTVMEA 6 OG - Partition plate



1465362

<https://www.phoenixcontact.com/in/products/1465362>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in