

Desktop Labelling machine



With safety often depending on it, in industry you can't afford to compromise on labelling. So the PT-9600 gives you industrial strength labelling. It's tough, but gives you all the options of our office labellers and more. All in a package designed to take the knocks whether you're on-site or not.

Key Features

- Save time up to 20mm per second
- 6, 9, 12, 18, 24 and 36mm wide durable labels available
- Standalone and PC Connectable
- Convenient built-in advanced automatic cutter
- Easy to use QWERTY keyboard
- Easy-to-read backlit LCD screen
- Includes 24mm black on white tape (8m), AC Adapter and rechargeable battery pack.

Supplies

	6 mm	9 mm	12 mm	18 mm	24 mm	36 mm
Standard - 8m						
	TZe-111	TZe-121	TZe-131	TZe-141	TZe-151	TZe-161
			TZe-132			
			TZe-133			
			TZe-135	TZe-145		
	TZe-211	TZe-221	TZe-231	TZe-241	TZe-251	TZe-261
			TZe-231S*			
		TZe-222	TZe-232	TZe-242	TZe-252	TZe-262
		TZe-223	TZe-233	TZe-243	TZe-253	TZe-263
			TZe-334	TZe-344	TZe-354	
	TZe-315	TZe-325	TZe-335	TZe-345	TZe-355	TZe-365
		TZe-421	TZe-431	TZe-441	TZe-451	TZe-461
			TZe-431S*			
			TZe-435			
		TZe-521	TZe-531	TZe-541	TZe-551	TZe-561
			TZe-535		TZe-555	
	TZe-611	TZe-621	TZe-631	TZe-641	TZe-651	TZe-661
		TZe-721	TZe-731	TZe-741	TZe-751	
Standard - 5m			TZe-B31		TZe-B51	
			TZe-C31		TZe-C51	
Standard - 3m			TZe-M31			
			TZe-MOL35**			
			TZe-MQP35**			
			TZe-MQG35**			
Standard - 8m			TZe-M931		TZe-M951	TZe-M961
Standard - 5m						
		TZe-N221	TZe-N231	TZe-N241	TZe-N251	
Standard - 8m						
	TZe-FX211	TZe-FX221	TZe-FX231	TZe-FX241	TZe-FX251	TZe-FX261
	TZe-FX611	TZe-FX621	TZe-FX631	TZe-FX641	TZe-FX651	TZe-FX661
Standard - 8m						
	TZe-S121	TZe-S131	TZe-S141	TZe-S151		
	TZe-S211	TZe-S221	TZe-S231	TZe-S241	TZe-S251	TZe-S261
		TZe-S621	TZe-S631	TZe-S641	TZe-S651	
Standard - 8m			TZe-FA3	TZe-FA4B		
Standard - 8m				TZe-SE4		

Optional Extras

-

Product Specifications

Housing Colour	Black
Key Board	QWERTY
Number of Keys	58
Cutter	Yes (automatic)
Power	AC adapter and Rechargeable Battery pack (BA9000) (Both included)
LCD	Backlit 20 chrs x 3 line
Print Method	Thermal
Print Head	360dpi
Print Speed	20 mm / sec
Tape Type	TZe
Tape Width	Max. Label width 36mm
Max. Print Width	27mm
Number of Characters	135
Number of Symbols	449
Character Sizes	96 (4 widths x 24 Heights)
Fonts	10 (Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Brunei Bold, Bermuda script, Istanbul and Letter Gothic)
Font Styles	18
Frames	30 kinds
Underline	Yes
Strikeout	Yes
Multi-Line	16 Lines
Multi-Block	Yes (Max 51 blocks)
Horizontal Alignment	Left (Centre, Right and Just)
Vertical Alignment	PT Editor Software
Tape Length Setting	Yes (60-999mm)
Tape Margin Setting	20-999mm
Memory	10240 characters 100 areas
Barcodes	Yes (9 kinds)
Numbering	Yes
Mirror Printing	Yes
Vertical Printing	Yes
Repeat printing	Yes
Print Preview	Yes
Language Change	-

Weights/ Dimensions/ Measures

Dimensions

237mm x 302mm x 104mm

Weight

2kg

What's in the box

24mm Black on White Laminated tape (8M)

AC Adapter

Rechargeable battery pack

Users Guide

Warranty Card

Tape catalogue