

## ABUS Analogue HD Video Surveillance 6-Channel Hybrid complete set

Art.-Nr. TVVR33621D

---

- Complete set with 6-channel analog hybrid recorder, two 2Mpx cameras, 1TB HDD, two 30m combo cables
  - Incl. 2 Mpx cameras for indoors and outdoors
  - Detailed Full HD (2MPx) resolution with 1920 x 1080 pixels at 25 fps
  - Ultra Low-Light function and noise reduction (DNR) for more detail even in very low light conditions
  - WDR (120 dB) for more detail even in backlighting and strong contrasts
  - Flexible integration: up to 4 analog HD cameras with 2 MPx and simultaneously 2 IP cameras with up to 6 MPx. Use completely with IP cameras if required
  - User-friendly app, web & PC software for live viewing and playback of video data
  - Easy mobile access with the ABUS Link Station App - no router settings required
  - Incl. 1 TB WD Purple Surveillance hard disk optimized for "nonstop" recordings
  - Recording via motion detection, following a time schedule or continuously
- 

The Analog HD set for immediate use contains everything you need for video surveillance in Full HD resolution: the recorder including 1 TB hard disk, 2 Analog HD cameras with 2MPx and 2 combo cables. Access to live images and recording is available via free app, web or CMS software - designed and supported in Germany.

Use advantages: Combine Analog HD and IP easily

The 6-channel hybrid recorder records video streams from 4 analog HD cameras and 2 compatible IP cameras in parallel - with 25 frames per second and a resolution of up to 4MPx per analog HD and 6MPx per IP camera. It supports the popular analog video formats TVI, AHD, CVI and CVBS, making it perfect for upgrading existing analog systems.

Easy commissioning and precise configuration

In just a few steps, the recorder is completely ready for operation and can be operated via monitor and mouse. Depending on requirements, it records manually as well as by motion detection, stored schedule or permanently - thanks to H.265 Plus for strong compression of the video data 6x longer compared to H.264. Several modes help in the efficient search and playback. Access is via local user interface, web interface, CMS software or app - even from a distance.

Access to live images and recordings via App: secure and easy

The recorder simply connects directly to the ABUS Link Station app on the smartphone or tablet via an encrypted end-to-end connection (E2E) - without any router settings. With the Lite version of the app, up to 60 minutes of data stream (live view/playback) per month via Internet or WLAN are completely free. Or with the ABUS Link Station Pro: Buy once and access unlimited data forever.

# ABUS Analogue HD Video Surveillance 6-Channel Hybrid complete set

Art.-Nr. TVVR33621D

Scope of delivery 01 description	6-Channel Hybrid Recorder (TVVR33600)	Scope of delivery 09 quantity	2
Scope of delivery 01 quantity	1		
Scope of delivery 02 description	2MPx Mini dôme-caméra (HDCC32561)		
Scope of delivery 02 quantity	2		
Scope of delivery 03 description	Power supply, 12V DC		
Scope of delivery 03 quantity	3		
Scope of delivery 04 description	30m combination cable		
Scope of delivery 04 quantity	2		
Scope of delivery 05 description	3,5" 1TB WD Purple SATA HDD		
Scope of delivery 05 quantity	1		
Scope of delivery 06 description	1m Network cable		
Scope of delivery 06 quantity	1		
Scope of delivery 07 description	USB wireless mouse incl. batteries		
Scope of delivery 07 quantity	1		
Scope of delivery 08 description	CD		
Scope of delivery 08 quantity	1		
Scope of delivery 09 description	Mounting material		