

Aluminium Electrolytic Capacitors

CCC-13

(1 Flap FL16/20) 16 Values / 270 Pieces
Cylindrical Aluminium-Can with radial leads

Type/Brand: 038 RSU / Vishay or alternative

Tolerance: ±20%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0 uF/63V	40x	22 uF/50V	25x	100uF/63V	14x	1000uF/16V	6x
2,2 uF/63V	25x	47 uF/25V	25x	220uF/35V	8x	1000uF/35V	4x
4,7 uF/63V	30x	47 uF/50V	25x	470uF/16V	6x	2200uF/35V	3x
10 uF/63V	30x	100uF/16V	20x	470uF/35V	6x	4700uF/16V	3x

CCC-14

(1 Flap FL16/20) 16 Values / 270 Pieces
Cylindrical Aluminium-Can with radial leads

Type/Brand: SE-K / TEAPO or Yageo Europe

Tolerance: ±20%

Temperature: -40 to +105°C

Values-Quantities Selection:

1,0uF/63V	40x	22uF/63V	25x	100uF/63V	14x	1000uF/16V	6x
2,2uF/63V	25x	47uF/25V	25x	220uF/35V	8x	1000uF/35V	4x
4,7uF/63V	30x	47uF/63V	25x	470uF/16V	6x	2200uF/35V	3x
10 uF/63V	30x	100uF/16V	20x	470uF/35V	6x	4700uF/16V	3x

CCC-15

(1 Flap FL16/20) 16 Values / 243 Pieces
Cylindrical Aluminium-Can with axial leads

Type/Brand: 021 ASM / Vishay

Tolerance: ±20%

Temperature: -40 to +85°C

Values-Quantities Selection:

1,0uF/63V	40x	22uF/63V	20x	100uF/63V	6x	1000uF/16V	4x
2,2uF/63V	30x	47uF/25V	25x	220uF/40V	6x	1000uF/40V	3x
4,7uF/63V	30x	47uF/63V	15x	470uF/16V	6x	2200uF/40V	2x
10 uF/63V	30x	100uF/25V	20x	470uF/40V	4x	4700uF/16V	2x

REV: 12.05.2009

CCC-16**(1 Flap FL16/20) 16 Values / 655 Pieces****Miniature Cylindrical Aluminium-Can with radial leads (4Øx7, 5Øx7, 6Øx7)****Type/Brand:** SS / TEAPO or Yageo Europe**Tolerance:** ±20%**Temperature:** -40 to +105°C**Values-Quantities Selection:**

0,10uF/63V	50x	1,0uF/63V	50x	4,7uF/63V	50x	33uF/ 25V	20x
0,22uF/63V	30x	2,2uF/36V	40x	10uF/ 16V	50x	47uF/ 6,3V	50x
0,33uF/63V	20x	3,3uF/63V	25x	10 uF/35V	50x	47uF/ 16V	50x
0,47uF/63V	50x	4,7uF/25V	50x	22 uF/35V	30x	100uF/6,3V	40x

CCC-17**(1 Flap FL16/20) 16 Values / 167 Pieces****Aluminium Electrolytic, radial, Low ESR****Type/Fab.:** SY / TEAPO**Tolerance:** ±20%**Temperature:** -40 to +105°C

see SY by TEAPO (PDF)

Values-Quantities Selection:

1000uF/16V	8x	2200uF/16V	4x	100uF/25V	25x	470uF/25V	10x
1000uF/25V	6x	2200uF/25V	4x	4700uF/25V	2x	47uF/35V	25x
220uF/35V	10x	470uF/35V	6x	1000uF/35V	4x	10uF/63V	40x
100 uF/63V	10x	220uF/63V	6x	470uF/63V	4x	1000uF/63V	3x

Chip Aluminium Electrolytic Capacitors**SMC-11****(1 Flap FL16/10) 16 Values / 290 Pieces****High Reliable Aluminium Electrolytic Capacitor in Chip form****Type/Brand:** MVK/NCC, SV/TEAPO or alternative D4/D5/D6 = diameter**Tolerance:** ±20%**Temperature:** -40 to +105°C**Values-Quantities Selection:**

0,10uF/50V (D4)	25x	2,2uF/50V (D4)	25x	6,8uF/25V (D5) **	10x	22uF/35V (D6)	10x
0,22uF/50V (D4)	25x	3,3uF/50V (D4)	15x	10uF/16V (D4)	20x	33uF/35V (D6)	10x
0,47uF/50V (D4)	25x	4,7uF/35V (D5)	25x	10uF/50V (D5)	20x	47uF/16V (D6)	10x
1,0uF/50V (D4)	25x	4,7uF/50V (D5)	25x	22uF/ 6V (D4)	10x	100uF/ 6V (D6)	10x

** delivery of alternative 10uF/35V (D5) possible

REV: 12.05.2009