

716077

# Ultra Hygiene Squeegee, 600 mm, Lime



This ultra-hygienic squeegee combines ultimate hygiene with effective water removal from walls, floors and tables. The angled blade makes it easy to remove water from corners and other difficult-to-reach areas, and the splash guard ensures that liquid does not spill onto the dried surface.

# Technical Data

<b>Item Number</b>	716077
<b>Material</b>	Polypropylene TPE Rubber
<b>Complies with (EC) 1935/2004 on food contact materials<sup>1</sup></b>	Yes
<b>Produced according to EU Regulation 2023/2006/EC of Good Manufacturing Practice</b>	Yes
<b>FDA compliant raw material (CFR 21)</b>	Yes
<b>Meets the REACH Regulation (EC) No. 1907/2006</b>	Yes
<b>Use of Phthalates</b>	No
<b>Is Halal compliant</b>	Yes
<b>Box Quantity</b>	10 Pcs.
<b>Quantity per Pallet (80 x 120 x 200 cm)</b>	480 Pcs.
<b>Quantity Per Layer (Pallet)</b>	60 Pcs.
<b>Box Length</b>	615 mm
<b>Box Width</b>	295 mm
<b>Box Height</b>	210 mm
<b>Length/Depth</b>	600 mm
<b>Width</b>	80 mm
<b>Height</b>	95 mm
<b>Gross Weight</b>	0,39 kg
<b>Net Weight</b>	0,36 kg
<b>Cubik metre</b>	0,0046 M3
<b>Recommended sterilisation temperature (Autoclave)</b>	121 °C
<b>Max. cleaning temperature (Dishwasher)</b>	93 °C
<b>Max. usage temperature (for food contact)</b>	50 °C
<b>Max usage temperature (non food contact)</b>	100 °C
<b>Min. usage temperature<sup>3</sup></b>	-20 °C
<b>Min. pH-value in usage concentration</b>	2 pH
<b>Max. pH-value in Usage Concentration</b>	10,5 pH
<b>GTIN-13 Number</b>	5705022014909
<b>GTIN-14 Number (Box quantity)</b>	15705028014931
<b>Commodity Code</b>	96039099
<b>Country of origin</b>	Denmark

New equipment should be cleaned, disinfected, sterilised and any labels removed, as appropriate to its intended use, e.g. high risk vs. low risk food production areas, general hospital areas vs. intensive care units, before use.

1. See Declaration of Compliance for further details on food contact

3. Do not store the product below 0° Celsius.