

Endress+Hauser TMT84-B1A2A

iTEMP TMT84, Transmitter PA



Picture for reference only. Product appearance may vary based on configuration

Dual sensor input. Advanced diagnostics: sensor monitoring. PROFIBUS PA Profile 3.02.

Configuration of TMT84-B1A2A:

Approval:	B1	ATEX II1G Ex ia IIC T4/T5/T6
Output Signal:	A	PROFIBUS PA
Electrical Connection:	2	Screw terminals, housing form B, DIN EN 50446
Field Housing:	A	W/o, mounting set DIN terminal head

Alternative part number: TMT84-10R4/0