



DWE4217

1200W 125mm Slide Switch SAG No-Volt

Selling Proposition

- No-volt release switch prevents the unit from starting unintentionally when locked on. Switch must be consciously reset before power is delivered
- Dust ejection system removes majority of debris from the air which passes over the motor, preventing abrasion and tracking
- High efficiency motor design improves performance in demanding applications
- Soft start reduces movement of the tool on startup increasing user control
- Small girth allow comfortable gripping resulting in superior ergonomics
- The compact gear case allows access in confined areas

Standard Equipment

- Protective keyless guard
- Multi-position side handle
- Inner and outer disc flange
- Spanner

Warranty Specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Power Input	1200 Watts
No Load Speed	11000 rpm
Max. Disc Diameter	125 mm
Spindle Thread	M14
Weight	2.2 kg
Length	285 mm
Height	80 mm
Hand/Arm Vibration - Grinding	8.3 m/s ²