



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Receptacle**
Connector System: **Wire-to-Board**
Number of Positions: **9**
Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	2 + 3
Number of Positions	9
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Locking Latch Between Cavity Number	1 + 2, 8 + 9
-------------------------------------	--------------



Mating Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Housing Material	PA 6.6
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Method	Bag & Box
Packaging Quantity	2000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits





as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1703133-1 9POS MT - EDGE HOUSING	 TE Part # 1-1703079-1 3POS MT-EDGE HOUSING	 TE Part # 1703079-1 3POS MT - EDGE HOUSING	 TE Part # 928017-1 6P MT-EDGE GEH
 TE Part # 1-1703080-1 3POS MT - EDGE HOUSING	 TE Part # 1-1703082-1 3POS MT - EDGE HOUSING	 TE Part # 1-1703083-1 3POS MT - EDGE HOUSING	 TE Part # 1703136-1 10POS MT - EDGE HOUSING

Also in the Series | RAST 5D

 Connector Contacts(12)	 Insertion & Extraction Tools(1)	 PCB Headers & Receptacles(417)	 Power Contacts(3)
 Rectangular Power Connectors(481)	 Wire-to-Board Connector Assemblies & Housings(197)	 Wire-to-Board Headers & Receptacles (417)	

Also in the Series | RAST 5 IDC Connectors



Connector Contacts(12)



Power Contacts(3)



Rectangular Connector Housings(1)



Rectangular Power Connectors(481)



Standard Edge Connectors(31)



Wire-to-Board Connector Assemblies & Housings(197)

Customers Also Bought




TE Part #1703129-1
8POS MT - EDGE HOUSING



TE Part #2-963860-1
TAB 2.8x0.8 CONTACT CF SRC Sn



TE Part #926972-1
MT-EDGE CRIM CONTACT



TE Part #284208-1
AMP MONO-SHAPE PCB 8 WAYS ASS'



TE Part #1703119-1
7POS MT - EDGE HOUSING



TE Part #926770-1
MT.EDGE CRIMP CONT.



TE Part #4-1105050-1
HN.D-C-STI.AG.1,5



TE Part #1703132-1
9POS MT - EDGE HOUSING

Documents

Product Drawings
9POS MT - EDGE HOUSING

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1703133-5_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1703133-5_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1703133-5_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English