

Plastic tubing PFAN-8X1,25-NT

Part number: 197063

FESTO



General operating condition

Data sheet

Feature	Value
Outside diameter	8 mm
Flow-relevant bending radius	110 mm
Inside diameter	5.9 mm
Min. bending radius	25 mm
Instructions on use	Tubing without printing
Symbol	00997424
Operating pressure complete temperature range	-0.095 MPa ... 0.6 MPa
Operating pressure complete temperature range	-0.95 bar ... 6 bar
Operating pressure complete temperature range	-13.775 psi ... 87 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1.5 MPa
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Temperature-dependent operating pressure	-13.775 psi ... 217.5 psi
Note on operating pressure	Water: max. 0.6 MPa at 0 - 85 °C Water vapour: 0 - 0.15 MPa, 0 - 1.5 bar, 0 - 22 psi
Operating medium	Compressed air to ISO 8573-1:2010 [7:--] Water (liquid, ice-free) Water vapour
Fire test material	UL94 V-0
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom class	Element installed statically, no meaningful evaluation possible according to ISO 14644-1
Suitable for use with food	See supplementary material information See declaration of conformity
Note on temperature of medium	Water vapour: max. 120 °C
Ambient temperature	-20 °C ... 150 °C
Product weight according to length	0.049 kg/m
Pneumatic connection	For push-in connector O.D. 8 mm For barbed fitting inside diameter of 6 mm with union nut For barbed fitting inside diameter of 6 mm
Colour	Natural
Shore hardness	D 60 +5
Note on materials	RoHS-compliant
Material tubing	PFA