



- Soldering Bath
- WSB 80 Solder Bath 80 W - 24 V
- Accessory for WT series soldering stations and WR series rework stations
- For tin coating and preparation of small electronics components and leads
- Precision temperature control / 150° F - 850° F / 50° C - 450° C
- Heated surface - 80 W: Soldering bath - Ø 0.8" x 0.98" D / Ø 20.3 mm x 24.9 mm D
- For lead free solder
- Heat-up time ~ 7 min (50 °C - 350 °C)
- For lead free solder

### WSB 80 Soldering bath

Product no.: T0052704099N

Dimensions L x W x H (mm)	150 x 120 x 70
Dimensions L x W x H (inches)	5.91 x 4.72 x 2.76
Weight (approx.) in kg	---
Voltage	24 V
Power	80 W
Channels	---
Temperature range (depends on tool) °C	66 - 343
Temperature range (depends on tool) °F	150 - 650
Temperature accuracy °C	---
Temperature accuracy °F	---
Temperature accuracy for hot air °C	---
Temperature accuracy for hot air °F	---
Temperature stability °C	---
Temperature stability °F	---
Equipotential bonding socket	---
Display	---
Additional vacuum pump	---
Max. hot air flow rate l/min (depends on tool)	---
Capacity l/min	---
Max. vacuum	---
Interface	---