

LED Bulkhead Lights

Features

- LED slim bulkhead solution for use in construction and site temporary settings
- 10W, 1200lm, 6000K, IP65, wide voltage 110-240V
- Polycarbonate body with an opal diffuser
- Suitable for wall, ceiling, scaffolding bar or hoarding lighting
- Designed with 6x 20mm conduit knockouts options for rear, top and bottom cable entry
- Integrated LED Tray
- IP65 rating for total protection against dust and low -pressure jets of water from any direction
- 2-year guarantee

RS PRO 10W 6000K IP65 SLIM BULKHEADS 110-240V

RS Stock No.: 0556561



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Buy this product from <https://uk.rs-online.com/>

Page 1 of 3

LED Bulkhead Lights

RS PRO's robust and reliable LED bulkheads provide an ideal lighting solution for construction sites, including areas around scaffolding and other confined spaces. Supplied with polycarbonate body with an opal diffuser.

General Specifications

Light Source Luminosity	1200lm
Efficiency	120lm/W
Beam Angle	120°
Colour Temperature	6000K Daylight
Light Source	Integral LED
Construction	Polycarbonate
Finish	Black/Opal
Energy Efficiency	E
Lifespan	50,000 Hours
Warranty	2 Years

Electrical Specifications

Wattage	10W
Voltage Rating	110-240V
Running Current	0.046A
Power Factor	0.85

Mechanical Specifications

Length	230mm
Width	110mm
Depth	100mm
Weight	0.25Kg

Protection Category

LED Bulkhead Lights

IP Rating	IP65
IK Rating	IK06

Operation Environment Specifications

Working Temperature	-10oC to +40oC
---------------------	----------------

Approvals

Compliance/Certifications	LVD, EMC, RoHS
Standards Met	BS EN 60598-1