

CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888  
<https://www.phoenixcontact.com/in/products/1202888>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping tool, for turned contacts, universal cross-section setting, up to a maximum of 6.0 mm<sup>2</sup>, digital display with 0.01 mm increments, pressure lock can be unlocked, positioning tool necessary as an accessory for contact positioning

Your advantages

- Electronic wear monitoring with recalibration function
- Process reliability with pressure lock and setting lock
- Basic setting testing with accompanying test pin
- Safe and simple handling with digital display and optional positioning aid
- Rotating positioning aid ensures precise contact positioning in the crimping area

Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1202888       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH3           |
| Product key                          | BH3135        |
| GTIN                                 | 4063151267711 |
| Weight per piece (including packing) | 1,140.7 g     |
| Weight per piece (excluding packing) | 1,140.7 g     |
| Customs tariff number                | 82032000      |
| Country of origin                    | DE            |

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## Technical data

### Notes

|                         |                                                                                                                                                                                                                                 |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Note on application     | The packing slip includes a detailed list of crimp contacts for turned crimp contacts from 0.14 mm <sup>2</sup> ...4.0 mm <sup>2</sup> of the series CK1.6 ED..., CK2.5 ED..., CK4.0 ED..., CC1.5-TS-2,10..., CC1.5-TS-2,50..., |
| Note on application     | Use with locator only; see accessories for selection                                                                                                                                                                            |
| Utilization restriction |                                                                                                                                                                                                                                 |
| EMC note                | EMC: class A product, see manufacturer's declaration in the download area                                                                                                                                                       |

### Product properties

|                  |                                                        |
|------------------|--------------------------------------------------------|
| Product type     | Crimping tool                                          |
| Compression      | Four-mandrel crimping                                  |
| Product property | Electronic wear monitoring with recalibration function |
|                  | Unlockable pressure lock                               |
|                  | Optional positioning tool                              |

### Crimping position 1

|                    |                      |
|--------------------|----------------------|
| Min. cross section | 0.14 mm <sup>2</sup> |
| Max. cross section | 6 mm <sup>2</sup>    |
| AWG min            | 26                   |
| AWG max            | 10                   |

### Connection data

#### Conductor connection

|                             |                                            |
|-----------------------------|--------------------------------------------|
| Cross section range, metric | 0.14 mm <sup>2</sup> ... 6 mm <sup>2</sup> |
| Cross section range AWG     | 26 ... 10                                  |

### Dimensions

|        |        |
|--------|--------|
| Width  | 94 mm  |
| Height | 28 mm  |
| Length | 236 mm |

### Material specifications

|          |                  |
|----------|------------------|
| Color    | black (RAL 9005) |
| Material | Steel            |

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1202888>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888  
<https://www.phoenixcontact.com/in/products/1202888>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 21043811 |
| ECLASS-12.0 | 21043811 |
| ECLASS-13.0 | 21043811 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000168 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888  
<https://www.phoenixcontact.com/in/products/1202888>

## Environmental product compliance

|                                         |                                                                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                                                                                                                                                                   |
| Fulfills EU RoHS substance requirements | Yes                                                                                                                                                                                                                               |
| Exemption                               | 6(a)-I                                                                                                                                                                                                                            |
| China RoHS                              |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP)  | EFUP-50                                                                                                                                                                                                                           |
|                                         | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                           |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)     | Lead(CAS: 7439-92-1)                                                                                                                                                                                                              |
| SCIP                                    | 894d1c6f-7088-4bbd-a917-a42c74c7be7c                                                                                                                                                                                              |

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## Mandatory accessories

### CRIMPFOX-TC MP/LOC-1 - Spare locator

1142829

<https://www.phoenixcontact.com/in/products/1142829>

Locator for CRIMPFOX-TC MP6



---

## Accessories

### CK1,6-ED-0,37F AU - Crimp contact

1266279

<https://www.phoenixcontact.com/in/products/1266279>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.14 mm<sup>2</sup> ... 0.34 mm<sup>2</sup>, AWG 24 ... 22

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,37M AU - Crimp contact

1266267

<https://www.phoenixcontact.com/in/products/1266267>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.14 mm<sup>2</sup> ... 0.34 mm<sup>2</sup>, AWG 24 ... 22

---

## CK1,6-ED-0,37F AG - Crimp contact

1266249

<https://www.phoenixcontact.com/in/products/1266249>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.14 mm<sup>2</sup> ... 0.34 mm<sup>2</sup>, AWG 24 ... 22

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,37M AG - Crimp contact

1266193

<https://www.phoenixcontact.com/in/products/1266193>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.14 mm<sup>2</sup> ... 0.34 mm<sup>2</sup>, AWG 26 ... 22

---

## CK1,6-ED-0,50M AU - Crimp contact

1266270

<https://www.phoenixcontact.com/in/products/1266270>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> .. 0.5 mm<sup>2</sup>, AWG 20



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,50M AG - Crimp contact

1266195

<https://www.phoenixcontact.com/in/products/1266195>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK1,6-ED-0,50F AU - Crimp contact

1266282

<https://www.phoenixcontact.com/in/products/1266282>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,50F AG - Crimp contact

1266252

<https://www.phoenixcontact.com/in/products/1266252>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK1,6-ED-0,75M AU - Crimp contact

1266272

<https://www.phoenixcontact.com/in/products/1266272>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,75M AG - Crimp contact

1266450

<https://www.phoenixcontact.com/in/products/1266450>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-0,75F AU - Crimp contact

1266283

<https://www.phoenixcontact.com/in/products/1266283>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,75F AG - Crimp contact

1266259

<https://www.phoenixcontact.com/in/products/1266259>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-1,00M AU - Crimp contact

1266274

<https://www.phoenixcontact.com/in/products/1266274>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,00M AG - Crimp contact

1266244

<https://www.phoenixcontact.com/in/products/1266244>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> .. 1 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-1,00F AU - Crimp contact

1266288

<https://www.phoenixcontact.com/in/products/1266288>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,50M AU - Crimp contact

1266276

<https://www.phoenixcontact.com/in/products/1266276>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> .. 1.5 mm<sup>2</sup>, AWG 16

---

## CK1,6-ED-1,50M AG - Crimp contact

1266245

<https://www.phoenixcontact.com/in/products/1266245>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,50F AU - Crimp contact

1266290

<https://www.phoenixcontact.com/in/products/1266290>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK1,6-ED-1,50F AG - Crimp contact

1266263

<https://www.phoenixcontact.com/in/products/1266263>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,50F AU - Crimp contact

1273564

<https://www.phoenixcontact.com/in/products/1273564>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK2,5-ED-0,50M AG - Crimp contact

1273667

<https://www.phoenixcontact.com/in/products/1273667>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,50M AU - Crimp contact

1273601

<https://www.phoenixcontact.com/in/products/1273601>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> .. 0.5 mm<sup>2</sup>, AWG 20

---

## CK2,5-ED-0,50F AG - Crimp contact

1273612

<https://www.phoenixcontact.com/in/products/1273612>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,75F AG - Crimp contact

1273611

<https://www.phoenixcontact.com/in/products/1273611>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK2,5-ED-1,00M AU - Crimp contact

1273582

<https://www.phoenixcontact.com/in/products/1273582>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,00M AG - Crimp contact

1273665

<https://www.phoenixcontact.com/in/products/1273665>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> .. 1 mm<sup>2</sup>, AWG 18

---

## CK2,5-ED-1,00F AU - Crimp contact

1271379

<https://www.phoenixcontact.com/in/products/1271379>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,00F AG - Crimp contact

1273610

<https://www.phoenixcontact.com/in/products/1273610>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

---

## CK2,5-ED-1,50M AU - Crimp contact

1273581

<https://www.phoenixcontact.com/in/products/1273581>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> .. 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,50M AG - Crimp contact

1273664

<https://www.phoenixcontact.com/in/products/1273664>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK2,5-ED-1,50F AU - Crimp contact

1271375

<https://www.phoenixcontact.com/in/products/1271375>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,50F AG - Crimp contact

1273609

<https://www.phoenixcontact.com/in/products/1273609>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK2,5-ED-2,50M AU - Crimp contact

1273572

<https://www.phoenixcontact.com/in/products/1273572>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 2.5 mm<sup>2</sup> .. 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-2,50M AG - Crimp contact

1273663

<https://www.phoenixcontact.com/in/products/1273663>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

---

## CK2,5-ED-2,50F AU - Crimp contact

1271376

<https://www.phoenixcontact.com/in/products/1271376>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-2,50F AG - Crimp contact

1273607

<https://www.phoenixcontact.com/in/products/1273607>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

---

## CK2,5-ED-4,00M AG - Crimp contact

1273620

<https://www.phoenixcontact.com/in/products/1273620>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> .. 4 mm<sup>2</sup>, AWG 12



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-4,00M AU - Crimp contact

1273568

<https://www.phoenixcontact.com/in/products/1273568>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

---

## CK2,5-ED-4,00F AU - Crimp contact

1271372

<https://www.phoenixcontact.com/in/products/1271372>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: gold-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-4,00F AG - Crimp contact

1273604

<https://www.phoenixcontact.com/in/products/1273604>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

---

## CK4,0-ED-1,50M AG - Crimp contact

1274097

<https://www.phoenixcontact.com/in/products/1274097>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-1,50F AG - Crimp contact

1274089

<https://www.phoenixcontact.com/in/products/1274089>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK4,0-ED-2,50M AG - Crimp contact

1274094

<https://www.phoenixcontact.com/in/products/1274094>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-2,50F AG - Crimp contact

1274088

<https://www.phoenixcontact.com/in/products/1274088>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

---

## CK4,0-ED-4,00M AG - Crimp contact

1274093

<https://www.phoenixcontact.com/in/products/1274093>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> .. . 4 mm<sup>2</sup>, AWG 12

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-4,00F AG - Crimp contact

1274087

<https://www.phoenixcontact.com/in/products/1274087>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, lead-free, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> .. 4 mm<sup>2</sup>, AWG 12

---

## CK2,5-ED-4,00ST AG - Crimp contact

1663637

<https://www.phoenixcontact.com/in/products/1663637>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-4,00ST AU - Crimp contact

1674794

<https://www.phoenixcontact.com/in/products/1674794>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

---

## CK2,5-ED-2,50BU AG - Crimp contact

1663682

<https://www.phoenixcontact.com/in/products/1663682>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-2,50BU AU - Crimp contact

1674862

<https://www.phoenixcontact.com/in/products/1674862>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

---

## CK2,5-ED-2,50ST AG - Crimp contact

1663611

<https://www.phoenixcontact.com/in/products/1663611>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-2,50ST-S AG - Crimp contact

1663873

<https://www.phoenixcontact.com/in/products/1663873>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14, last make, first break contact

---

## CK2,5-ED-2,50ST AU - Crimp contact

1674817

<https://www.phoenixcontact.com/in/products/1674817>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,50BU AG - Crimp contact

1663679

<https://www.phoenixcontact.com/in/products/1663679>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK2,5-ED-1,50BU AU - Crimp contact

1674820

<https://www.phoenixcontact.com/in/products/1674820>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,50ST AG - Crimp contact

1663608

<https://www.phoenixcontact.com/in/products/1663608>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK2,5-ED-1,50ST-S AG - Crimp contact

1663860

<https://www.phoenixcontact.com/in/products/1663860>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16, last make, first break contact

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,50ST AU - Crimp contact

1674778

<https://www.phoenixcontact.com/in/products/1674778>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK2,5-ED-1,00BU AG - Crimp contact

1663666

<https://www.phoenixcontact.com/in/products/1663666>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,00BU AU - Crimp contact

1674833

<https://www.phoenixcontact.com/in/products/1674833>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

---

## CK2,5-ED-1,00ST AG - Crimp contact

1663598

<https://www.phoenixcontact.com/in/products/1663598>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-1,00ST-S AG - Crimp contact

1663857

<https://www.phoenixcontact.com/in/products/1663857>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18, last make, first break contact

---

## CK2,5-ED-0,75BU AG - Crimp contact

1663653

<https://www.phoenixcontact.com/in/products/1663653>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,75ST AG - Crimp contact

1663585

<https://www.phoenixcontact.com/in/products/1663585>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK2,5-ED-0,50BU AG - Crimp contact

1663640

<https://www.phoenixcontact.com/in/products/1663640>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,50BU AU - Crimp contact

1674859

<https://www.phoenixcontact.com/in/products/1674859>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK2,5-ED-0,50ST AG - Crimp contact

1663572

<https://www.phoenixcontact.com/in/products/1663572>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-0,50ST AU - Crimp contact

1674804

<https://www.phoenixcontact.com/in/products/1674804>



Crimp contact, contact diameter: 2.5 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK1,6-ED-1,50BU AG - Crimp contact

1663433

<https://www.phoenixcontact.com/in/products/1663433>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,50BU AU - Crimp contact

1674930

<https://www.phoenixcontact.com/in/products/1674930>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK1,6-ED-1,50ST AG - Crimp contact

1663378

<https://www.phoenixcontact.com/in/products/1663378>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,50ST AU - Crimp contact

1674875

<https://www.phoenixcontact.com/in/products/1674875>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## CK1,6-ED-1,00BU AG - Crimp contact

1663420

<https://www.phoenixcontact.com/in/products/1663420>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,00BU AU - Crimp contact

1674943

<https://www.phoenixcontact.com/in/products/1674943>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-1,00ST AG - Crimp contact

1663365

<https://www.phoenixcontact.com/in/products/1663365>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-1,00ST AU - Crimp contact

1674888

<https://www.phoenixcontact.com/in/products/1674888>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 1 mm<sup>2</sup> ... 1 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-0,75BU AG - Crimp contact

1663417

<https://www.phoenixcontact.com/in/products/1663417>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,75BU AU - Crimp contact

1672440

<https://www.phoenixcontact.com/in/products/1672440>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-0,75ST AG - Crimp contact

1663352

<https://www.phoenixcontact.com/in/products/1663352>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,75ST AU - Crimp contact

1674914

<https://www.phoenixcontact.com/in/products/1674914>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.75 mm<sup>2</sup> ... 0.75 mm<sup>2</sup>, AWG 18

---

## CK1,6-ED-0,50BU AG - Crimp contact

1663404

<https://www.phoenixcontact.com/in/products/1663404>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,50BU AU - Crimp contact

1674480

<https://www.phoenixcontact.com/in/products/1674480>



Crimp contact, contact diameter: 1.6 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK1,6-ED-0,50ST AG - Crimp contact

1663349

<https://www.phoenixcontact.com/in/products/1663349>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK1,6-ED-0,50ST AU - Crimp contact

1672453

<https://www.phoenixcontact.com/in/products/1672453>



Crimp contact, contact diameter: 1.6 mm, turned, Pin, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 0.5 mm<sup>2</sup> ... 0.5 mm<sup>2</sup>, AWG 20

---

## CK2,5-ED-4,00BU AG - Crimp contact

1663705

<https://www.phoenixcontact.com/in/products/1663705>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12



# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK2,5-ED-4,00BU AU - Crimp contact

1674846

<https://www.phoenixcontact.com/in/products/1674846>



Crimp contact, contact diameter: 2.5 mm, turned, Socket, contact material: Copper alloy, contact surface: gold-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

---

## CK4,0-ED-4,00BU AG - Crimp contact

1663297

<https://www.phoenixcontact.com/in/products/1663297>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-4,00ST AG - Crimp contact

1663255

<https://www.phoenixcontact.com/in/products/1663255>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 4 mm<sup>2</sup> ... 4 mm<sup>2</sup>, AWG 12

---

## CK4,0-ED-2,50BU AG - Crimp contact

1663284

<https://www.phoenixcontact.com/in/products/1663284>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-2,50ST AG - Crimp contact

1663242

<https://www.phoenixcontact.com/in/products/1663242>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 2.5 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, AWG 14

---

## CK4,0-ED-1,50BU AG - Crimp contact

1663271

<https://www.phoenixcontact.com/in/products/1663271>



Crimp contact, contact diameter: 4 mm, turned, Socket, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## CK4,0-ED-1,50ST AG - Crimp contact

1663239

<https://www.phoenixcontact.com/in/products/1663239>



Crimp contact, contact diameter: 4 mm, turned, Pin, contact material: Copper alloy, contact surface: silver-plated, connection cross section: 1.5 mm<sup>2</sup> ... 1.5 mm<sup>2</sup>, AWG 16

---

## UNIFOX RT-CK 1.6 - Contact removal tool

1072069

<https://www.phoenixcontact.com/in/products/1072069>



Contact removal tool, for turned and rolled CK- 1.6-... contacts

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display



1202888

<https://www.phoenixcontact.com/in/products/1202888>

## UNIFOX MT-CK 1.6/2.5 - Assembly tool

1089092

<https://www.phoenixcontact.com/in/products/1089092>



Assembly tool, for CK 1.6... crimp contacts for small conductor cross sections

---

## UNIFOX RT-CK 2.5 - Contact removal tool

1072067

<https://www.phoenixcontact.com/in/products/1072067>



Contact removal tool, for turned CK 2,5... contacts

# CRIMPFOX-TC MP-6 - Crimping pliers with digital display

1202888

<https://www.phoenixcontact.com/in/products/1202888>



## UNIFOX RT-CK 4.0 - Contact removal tool

1072064

<https://www.phoenixcontact.com/in/products/1072064>

Contact removal tool, for rotated CK-4,0-... contacts



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)