

Charge 'n' Go Magnetic Wireless Power Bank 10000mAh



Part Number: 32245, 32246, 32247, 32248, 32249

Description

The Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000mAh with its slim 16mm body and 15W magnetic wireless charging offers maximum portability and performance.

It also features PD20W capabilities, a bi-directional Type-C port for swift charging, an LED indicator to provide users with easy-to-monitor power status, and an additional metal ring that can be attached to the phone or phone case to provide a strong magnetic hold if required.

Designed for versatility, Verbatim Power Banks are perfect companions for travel, commuting, events, and outdoor activities, offering a dependable on-the-go energy solution

- High density battery
- Nominal capacity: 10000 mAh
- Slim body thickness - only 16mm
- 15W magnetic wireless charging
- PD 20W capabilities
- LED indicator for easy-to-read power status
- Bi-direction fast charging & discharging Type-C port



Charge 'n' Go Magnetic Wireless Power Bank 10000mAh



Part Number: 32245, 32246, 32247, 32248, 32249

Specifications:

Battery Capacity: 10000mAh

Rated Capacity: Based on 5V-2.4A output - Around 6000mAh

USB-C PD 3.0 Input:

5 V = 2.4 A, 9 V = 2.0 A (18 W max)

USB-C PD 3.0 Output:

5 V = 2.4 A, 9 V = 2.22 A, 12 V = 1.67 A, (20 W max)

Wireless Output: 5W, 7.5W, 10W, 15W

Total PD Output: 20 W max.

Supports PD 3.0, QC 3.0, Apple2.4A, BC1.2, DCP, AFC

Working Temperature: 0 °C to 35 °C

Storage Temperature: Under normal temperature conditions:-10 ~45°C;
charging and discharging every 3-4months



Languages

Front of pack: English (Product description also in French)

Back of pack: English, English; French; German; Dutch; Italian; Spanish;
Portuguese; Polish; Russian; Czech; Hungarian; Slovakian; Croatian; Serbian;
Romanian; Turkish; Traditional Chinese; Simplified Chinese; Korean;
Japanese

Quick Installation Languages:

EN/FR/DE + Multilingual support text

Pack Contents:

- Power Pack
- Metallic Ring
- USB-C to USB-C 30cm cable

Charge 'n' Go Magnetic Wireless Power Bank 10000mAh



Reorder No.	Description	Barcode	EAN-128	EAN-14
32245	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000 Black	023942322450	(02)00023942322450(37)10(91)843 (02)00023942322450(37)20(91)843	20023942322454 50023942322455
32246	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000 Green	023942322467	(02)00023942322467(37)10(91)843 (02)00023942322467(37)20(91)843	20023942322461 50023942322462
32247	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000 Blue	023942322474	(02)00023942322474(37)10(91)843 (02)00023942322474(37)20(91)843	20023942322478 50023942322479
32248	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000 Pink	023942322481	(02)00023942322481(37)10(91)843 (02)00023942322481(37)20(91)843	20023942322485 50023942322486
32249	Verbatim Charge 'n' Go Magnetic Wireless Power Bank 10000 Grey	023942322498	(02)00023942322498(37)10(91)843 (02)00023942322498(37)20(91)843	20023942322492 50023942322493



Charge 'n' Go Magnetic Wireless Power Bank 10000mAh



Ordering information:

Reorder No.	
Product Dimensions L x W x H	67 x 16 x 105 mm
Product Weight	187 grams
Units per Pack	1
Pack Dimensions L x W x H	90 x 30 x 128 mm (with hanger 158mm)
Pack Weight	247 grams
Units per Inner Carton	10
Inner Carton Dimensions L x W x H	275 x 180 x 118 mm
Inner Cartons Weight	2600 grams
Units per Outer Carton	20
Outer Carton Dimensions L x W x H	295 x 170 x 264 mm
Outer Cartons Weight	5500 grams
Outer Cartons per Layer	12
Layers per Pallet	5
Units per Pallet	1200

