



Einhell

PROFESSIONAL

POWER X-CHANGE

Professional

Cordless Circular Saw

TP-CS 18/190 Li BL - Solo

Item No.: 4331210

Ident No.: 21021

Bar Code: 4006825641547

The Einhell Cordless Handheld Circular Saw TP-CS 18/190 Li BL-Solo is part of the Power X-Change series and is compatible with all Einhell guide rails. The tool is powered by the Einhell PurePOWER brushless motor for more power and longer running time. After online registration, the motor comes with a 10-year warranty. The saw is easy to operate – with tool-free adjustment (cutting depth, tilt angle) and easy saw blade changes thanks to the spindle lock. The splitter adapts to the cutting depth, while the parallel stop and the carbide saw blade enable precise cuts. The high-quality baseplate is made of aluminum and is equipped with a dust extraction adapter. This product comes without a battery or charger.

Features & Benefits

- Member of the Power X-Change family, 1x 18V battery required
- Brushless motor - more power and longer running time
- PurePOWER Brushless - 10 years motor warranty after registration
- Easy adjustment without tools (cutting depth, tilt angle)
- Large handle for tireless working
- High-quality LED for optimum illumination of the cutting area
- High-quality baseplate made of aluminium
- Easy changing of the saw blade thanks to the spindle lock
- High-grade carbide blade for clean cuts
- Sawblade with 20mm and 30mm bore diameter can be used
- Dust extraction adapter to keep the workplace clean
- Compatible with the Einhell guide rail
- Parallel stop for precise cuts
- Supplied without battery and charger (available separately)



Technical Data

- | | |
|---|------------------------|
| - Cutting depth at 45° | 45 mm |
| - Cutting depth at 90° | 65 mm |
| - Idle speed max. | 3800 min ⁻¹ |
| - Motor voltage | 18 V |
| - Number of saw blades included in delivery | 1 pcs |
| - Product weight | 2.92 Kg |
| - Saw blade 1 diameter | 190 mm |
| - Saw blade holder diameter | 20 mm |

Logistic Data

- | | |
|--|-------------------------------|
| - Product weight | 2.92 kg |
| - Gross weight | 4.13 kg |
| - Dimensions single packaging | 351 mm x 219 mm x 326 mm |
| - Pieces per export carton | 2 pcs |
| - Gross weight of export carton | 10.05 kg |
| - Dimensions export carton | 460 mm x 369 mm x 342 mm |
| - Container quantities (20"/40"/40"HC) | 900 pcs 1940 pcs 2260 pcs |



Available as special accessories



Guide Rail, 2x 1000 mm
Circular Saw Accessory
Item No.: 4502118
Bar Code: 4006825632675
Einhell Accessory



E-Case L with Wheels
System Carrying Case
Item No.: 4540014
Bar Code: 4006825660562
Einhell Accessory



E-Case M
System Carrying Case
Item No.: 4540021
Bar Code: 4006825667721
Einhell Accessory



E-Case M SEALED
System Carrying Case
Item No.: 4540053
Bar Code: 4006825687071
Einhell Accessory



E-Case L with wheels SEALED
System Carrying Case
Item No.: 4540054
Bar Code: 4006825687088
Einhell Accessory



TCT Circular Saw Blade, Ø 190 x
30 x 2 mm, 30 T
Handkreissägen-Zubehör
Item No.: 49586956
Bar Code: 4009315869568



PXC 18V 3,0Ah
Battery
Item No.: 4511341
Bar Code: 4006825590593
Einhell Accessory



PXC 18V 2,0Ah
Battery
Item No.: 4511395
Bar Code: 4006825610369
Einhell Accessory



PXC 18V 4,0Ah C01
Battery
Item No.: 4511396
Bar Code: 4006825610376
Einhell Accessory



PXC 18V 5,2Ah
Battery
Item No.: 4511437
Bar Code: 4006825616606
Einhell Accessory



PXC+ 18V 3,0Ah
Battery
Item No.: 4511501
Bar Code: 4006825644197
Einhell Accessory



PXC+ 18V 4-6Ah MULTI
Battery
Item No.: 4511502
Bar Code: 4006825644210
Einhell Accessory



PXC 18V 2,5Ah
Battery
Item No.: 4511516
Bar Code: 4006825650518
Einhell Accessory



2x18V 4,0Ah PXC-Twinpack CB
Battery
Item No.: 4511489
Bar Code: 4006825638578
Einhell Accessory



Power X-Twincharger 3A
Charger
Item No.: 4512069
Bar Code: 4006825629729
Einhell Accessory



2x2 Power X-Quattrocharger 4A
Charger
Item No.: 4512102
Bar Code: 4006825649536
Einhell Accessory



Power X-Fastcharger 4A
Charger
Item No.: 4512103
Bar Code: 4006825650228
Einhell Accessory



Power X-Car Charger 3A
Charger
Item No.: 4512113
Bar Code: 4006825655377
Einhell Accessory



18V 2,0Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512040
Bar Code: 4006825613681
Einhell Accessory



18V 4,0Ah PXC Starter Kit C1
PXC-Starter-Kit
Item No.: 4512042
Bar Code: 4006825613704
Einhell Accessory



18V 2,5Ah PXC Starter Kit
PXC-Starter-Kit
Item No.: 4512097
Bar Code: 4006825646962
Einhell Accessory

Battery-Running-Times

Battery Capacity	2.5 Ah	3.0 Ah	4.0 Ah	5.2 Ah	6.0 Ah	8.0 Ah
Performance	30 m	37 m	49 m	63 m	73 m	98 m

Max. cutting capacity per battery charge: chipboard 19 mm
Recommendation for optimum results: 2.5 Ah battery & higher