

FEATURES

- Contact rating 12 A to 16A, 125-250Vac
- Rust and corrosion proof reinforced polymeric construction
- Non-skid base pad
- Rated to IP20
- Dark grey in colour
- Adjustable strain relief clamp for various cable sizes
- Flame retardant

RS PRO Light Duty Maintained Foot Switch - Polymer Case Material, SPST-NO, 12 A @ 250 V ac Contact Current, 250V

RS Stock No.: 116-748



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO light duty foot switches which are ideal for a number of applications. They have a light weight polymeric housing with non-skid base pads and the raised ribs on the cover ensure a good grip.

This range of light-duty foot pedal switches includes:

116-906 - Momentary SPDT

116-681 - Momentary DPDT

116-748 - Maintained SPST-NO

General Specifications

Contact Configuration	SPST-NO
Switch Operation	Maintained
Case Material	Polymer
Switch Environment	Light Duty
Colour	Dark grey
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	Adjustable strain relief clamp accommodates a wide range of cable sizes

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Current Rating	12A @ 250 V ac

Mechanical Specifications

Length	101.32mm
Height	27.76mm
Dimensions	101.32mm x 87.27mm x 27.76mm
Width	87.27mm
Weight	0.1kg

Protection Category

IP Rating	IP20
-----------	------

Approvals

Standards Met	EN60529
Compliance/Certifications	RoHS



[illegible]