

Endress+Hauser Graphic data manager RSG35-B2A

Recording, visualization and monitoring of process values.



Picture for reference only. Product appearance may vary based on configuration

The Ecograph T RSG35 is a Universal Data Manager that records, displays and monitors all analog or digital input signals. The measured values are securely saved and limit values are monitored. On-site, the navigator enables intuitive operation. Remote configuration and operation on the PC are also possible thanks to the integrated web server - no additional software needs to be installed.

- The recorded data is stored tamperproof in the internal memory or on a separate SD card.
- Intuitive operation via the navigator (rotary/ push button) on site, or user-friendly operation at the PC via the integrated web server
- Versatile with up to 12 universal inputs compatible with the most common measurement signals.
- Programmable e-mail notification in event of alarms and limit violation
- 5.7" TFT screen for displaying measured values in a maximum of four groups, with digital, bar graph and curve display.

Configuration of RSG35-B2A:

Input Signal:	B	4x universal
Power Supply:	2	24V (-10%; +15%) AC/DC
Communication:	A	Ethernet RJ45 + USB

Alternative part number: RSG35-1RJ0/0