

Combi Drill LXT®

DHP492

18V

A powerful, brushless general-use impact drill for screwdriving and drilling

An efficient, brushless drill for screwdriving and drilling. A powerful max. torque of 141Nm. The main feature and benefits are: Redesigned speed change mechanism to avoid gear disengagement, Controller protection has been revised to enhance the protection for electronic components during variable speed control by the trigger.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
No load speed	0 - 550 / 2100 min ⁻¹
Max. fastening torque Hard/Soft	130 / 65 Nm
Max Torque	141 Nm
Torque setting	21
Impacts per Minute (IPM)	0 - 8250 / 31500 min ⁻¹
Max. Drilling Diameter in Masonry	16 mm
Max. Drilling Diameter in Steel	13 mm
Drilling Capacity Wood (Auger Bit)	50 mm
Drilling Capacity Wood (Self-feed bit)	76 mm
Drilling Capacity Flat bit	40 mm
Drilling Capacity Hole Saw	152 mm
Driving Shank	1/2"-20UNF "

User benefits

- Highly efficient and compact machine for professional use
- LED light illuminates the work site
- Battery protection system automatically shuts off power when the battery level is low
- Electronic overload protection protects the user and the device
- Keyless chuck for easy bit installation and removal
- Compact and lightweight for reduced operator fatigue
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitaauk.com



Related products

Optional AC

122576-8

Stopper Pole



122D10-2

Grip Assembly



821550-0

Makpac case (2)



837916-4

MakPac (2) Inlay



Other

User manual

Parts drawing