



# 18Vx2 Chainsaw 350mm BL LXT DUC355Z

DUC305, DUC355 and DUC405 are cordless chainsaws powered by two 18V Li-ion batteries in series



## TECHNICAL SPECIFICATIONS

|                         |                           |
|-------------------------|---------------------------|
| Battery Type            | Lithium-ion               |
| Body only machine       | ✓                         |
| Voltage                 | 36 (18v x2) v             |
| Chain Oil Capacity      | 200 ml (cm <sup>3</sup> ) |
| Chain Gauge             | 0.043 "                   |
| Chain Pitch             | 3/8 "                     |
| Chain Speed             | 0-20 m/sec                |
| Bar Size                | 35 cm                     |
| Noise sound pressure    | 87.7 dB(A)                |
| Noise sound power       | 100.4 dB(A)               |
| Noise K factor          | 2 dB(A)                   |
| Maximum Output          | 1,100 w                   |
| Vibration K factor      | 1.5 m/sec <sup>2</sup>    |
| Vibration: Cutting Wood | 5.3 m/sec <sup>2</sup>    |
| Net weight              | 4.7 - 5.4 kg              |

## USER BENEFITS

- Captive nuts: prevent loss of nut when removing sprocket cover to replace guide bar or saw chain
- Brushless motor
- Variable speed control by trigger
- Constant speed control
- Electric chain brake
- Kickback brake
- Oil Capacity Display
- Ergonomic soft grip
- Large separate-type metal spike bumper. Spike grips work-piece firmly to provide more control.
- Adjustable automatic chain lubrication
- Lock-off lever
- Powered by two 18V Li-ion batteries in series to supply energy to the powerful 36V DC motor drive system.
- Main power switch with auto power-off function
- Battery protection system provides over-discharge protection for enhanced battery cycle life and overall battery life.

[Link to product - makitauk.com](https://www.makita.com)



# RELATED PRODUCTS

(Recom

## ■ OTHER