



ENGLISH

Datasheet

RS Pro 3W LED Emergency Surface Hanging Exit Sign

RS Stock No: 189-6585



This RS Pro LED Emergency Surface hanging Exit Sign is suitable for use in both Industrial and commercial applications, such as hospitals, factories, leisure facilities, schools and hotels. This product has legend kit supplied, with an adjustable hanging length for user's requirements. Supplied as a maintained fitting with 3 year warranty.



Typical Properties

ENGLISH

| | |
|----------------------------|-------------------------------------|
| Material | Polycarbonate Body, Acrylate Screen |
| Wattage | 3W |
| Supply Voltage | 200 – 240 50Hz |
| Battery | 3.6V 900mAh Ni-Cad |
| Colour Temperature | 6000k |
| Light Colour | Daylight |
| Emergency visible Distance | Up to 24m |
| Emergency Duration | Minimum 3 hours |
| Indicators | Green, battery charge |
| Product Colour | White |
| Maximum Hanging Length | 480mm |
| Dimmable | No |
| IP Rating | IP20 |
| Rated Life | 35,000 Hours |
| Warranty | 3 Years |

