

CZL240-12HRA



CU 45DEGREE LUG 240SQMM M12



General Information

Extended Product Type	CZL240-12HRA
Product ID	7TBH007940R0382
EAN	5415022378993
Catalog Description	CU 45DEGREE LUG 240SQMM M12
Long Description	Copper One-Hole 45 Degree Angle Metric Lug, Standard Barrel, Cable Size 240mm2, Stud Size M12, Length 74.9mm, Flat 39.5mm, Hole Spacing 21mm

Ordering

EAN	5415022378993
Minimum Order Quantity	200 piece
Customs Tariff Number	8536904000

Dimensions

Product Net Weight	246.562 g
--------------------	-----------

Container Information

Package Level 1 Width	199.898 mm
Package Level 1 Height	102.108 mm
Package Level 1 Depth / Length	72.898 mm
Package Level 2 Units	200 piece
Package Level 2 Width	320.04 mm
Package Level 2 Height	220.98 mm
Package Level 2 Depth / Length	215.9 mm
Package Level 3 Units	200 piece

Additional Information

Brand / Label	Spec-Kon
Insulation Material	None
Material	Copper
Product Main Type	COMPRESSION CONNECTORS
Product Name	COPPER LUG
Product Type	Copper One-Hole 45 Degree Metric Lug

UPC

786210083964

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	CZL240-12HRA
Instructions and Manuals	CZL240-12HRA

Classifications

ETIM 6	EC001051 - Tube cable lug for copper conductors
UNSPSC	39121405
WEEE Category	Product Not in WEEE Scope

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Compression & Mechanical Connectors

