

Main

Range of product	Mureva Styl
Product or component type	Key switch
Device presentation	Mechanism
Colour tint	Grey (RAL 7016)
Quantity per set	Set of 1

Complementary

Device mounting	Surface Flush
Technology type	Electromechanical
[Us] rated supply voltage	230 V AC 50/60 Hz
Rated current	3 A
Switch function	2 positions
Key withdrawal position	Center
Condition of use	Indoor/outdoor
Material	ABS (acrylonitrile butadiene-styrene) PP (polypropylene)
Fixing mode	By screws
Height	71 mm
Width	71 mm
Depth	72 mm

Environment

Quality labels	EAC CE
IP degree of protection	IP55
IK degree of protection	IK08
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

Offer Sustainability

REACH Regulation	 REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration