




P	LTR	DESCRIPTION	ECN	DATE	DWN	APVD
	O	RELEASED	FJ00-3023-95	7/31'95	TS	AT
	A	REVISED	FJ00-0253-97	2/20'97	TS	AT



— 1 ; 本 ☒



SECT. A-A



SECT. B-B




注 :

1. 適用圧着規格番号 : 114-5193

NOTES;

1. APPLICABLE CRIMPING SPEC No. 114-5193

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.DIMENSIONS,
単位 規
mmMATERIAL
材料

PRE-TIN

錫メッキ黄銅0.2t

TOLERANCES UNLESS
OTHERWISE SPECIFIED一般公差
10mm : ±0.2
30mm : ±0.25
100mm : ±0.3
ANGLE : ±0.3°FINISH
仕上

—

DWN 7/31'95
T. SHINOHARA
CHK 7/31'95
K. YUASA
APVD 7/31'95
A. TOMITAPRODUCT SPEC
製品規格APPLICATION SPEC
取付運用規格

WEIGHT

0.06g

CUSTOMER DRAWING

WIRE RANGE
包合電線断面積

AWG #22~#20 (0.3~0.5)

INSULATION DIA
被覆外径

1.4~1.7

AMP

日本エー・エム・ジー株式会社
Kawasaki, JapanNAME
名称TAB CONTACT (MINI MULTI LOCK CONN)
タブ コンタクト (ミニ・マルチ・ロック コネクタ)

SIZE

CAGE CODE

DRAWING NO
番号

A3

00779

917309

SCALE
尺度

10-1

SHEET 1 OF 1

REV A