

ReXel Optimum AutoFeed+ 50X Automatic Cross Cut Paper Shredder

The Optimum AutoFeed+ 50X cross cut shredder automatically shreds up to 50x A4 sheets of paper (80gsm) at a time, into P-4 (4x28mm) cross cut pieces. This auto feed shredder machine is ideal for use as a home or home office shredder due to its compact 20L bin. No need to manually feed paper, or remove staples and paper clips first, this automatic paper shredder will do all the work for you.



Attributes

- Auto feed up to 50 sheets of A4 paper (80gsm) at a time. Manual slot for up to 6 sheets.
- P-4 cross cut (4x28mm)
- 20L capacity pull out bin
- Anti-jam technology
- Shreds credit cards, staples and paper clips
- 10 minutes continuous run time with fan cooling
- Touch control panel
- 55 dBA ultra-quiet noise level
- Infra red bin full sensor
- 2 year warranty, 2 year cutter warranty



Specifications

Number	2020050X
Colour	black
Dimensions (W x H x D)	363 x 405 x 430 mm
Cut Type	Cross Cut
Maximum Slot Entry Width (mm)	220
Run Time From Cold (min)	10
Shredded Particle Width mm	4x28
Security Level	P-4
Cutting Capacity sheets (70gsm paper)	55
Cutting Capacity sheets (80gsm paper)	50
Container/collection volume in l	20
Shreds	Paper, Credit cards, Paper clips & Staples
Power consumption (W)	200
Noise Level (dBA)	55
Period of Warranty (Years)	2
Location	Personal / Home Office
Number Of Users	1-2
Weight	11600 g
Pallet quantity	12
EAN code	5028252606219