

PRODUCT-DETAILS

TYZ27M

CABLE TIE 120LB 13IN AQUAMARIN ETFE



General Information

Extended Product Type	TYZ27M
Product ID	7TAG009620R0004
EAN	5414363068143
Catalog Description	CABLE TIE 120LB 13IN AQUAMARIN ETFE
Long Description	High Performance Cable Tie, Aquamarine Fluoropolymer ETFE for Temperatures up to 150 Degrees Celsius (302 F), Length of 343mm (13.5 Inches), Width of 6.9mm (0.27 Inch), Thickness of 1.8mm (0.07 Inch), Tensile Strength Rating of 534 Newtons (120 Pounds), Bulk Pack

Ordering

EAN	5414363068143
UPC	786210872926

Dimensions

Product Net Width	0.27 in 6.9 mm
Product Net Depth / Length	13.5 in 343 mm

Container Information

Package Level 1 Units	100 piece
-----------------------	-----------

Package Level 1 Width	6 in 152 mm
Package Level 1 Depth / Length	27 in 686 mm
Package Level 2 Units	500 piece
Package Level 2 Width	5.6 in 142 mm
Package Level 2 Height	10 in 254 mm
Package Level 2 Depth / Length	15.7 in 399 mm

Technical UL/CSA

Flammability According to UL94	V-0
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.5 to 3.5 in 12.7 to 88.9 mm
Color	Aqua
Effective Date	19741228
Lock Type	Stainless Steel Barb
Material	Fluoropolymer ETFE
Number of Batteries	0
Product Name	NYLON CABLE TIES AND ACCESSORIES
Product Type	Radiation Resistant
Standards	UL E49405
Tensile Strength	120 lb 534 N
Thickness	0.07 in 1.8 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000517
Instructions and Manuals	TYZ27M
REACH Declaration	9AKK107992A8793
RoHS Information	9AKK107991A8362

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

