



See online
technical sheet

/ MS45

1000V Insulated cable cutting pliers



/ Standards

EN 60900 / IEC 60900

/ Use

For cutting electrical cables.

/ Technical specifications

Automatic opening, invisible spring.
Clamp with locking lever for extra safety.
Cutting capacities indicated on the tool.

/ Table legend

Overall length tolerance : ± 10 mm of the nominal value.

Advantages

The ground blades with a specific cutting angle allow a clean and sharp cut.

Product reference	Diameter (Ø) cutting capacity	Jaw opening diameter	Length	Poids
MS45-195	-	Ø 20 mm	195 mm	430 g
MS45 230	Ø 12 mm	-	250 mm	470 g