

CURRENT RATING:	5 A
CONTACT RESISTANCE:	15
INSULATION RESISTANCE:	1,0
WORKING VOLTAGE:	250
TEMPERATURE:	-55

5 AMPS 15 mOhms Max. 1,000 MOhms min. 250VAC -55° C TO 125° C

RoHS COMPLIANT

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE				DATE: 9-4-08		
BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.						
		SCALE:	SHEET	OF		REV
NorComp		NTS		1	3	10
NorComp		DWG NO. 772-EYY-213RYY1				

DIMENSIONS (inch mm)

D

Е


F

С

В

No. OF

А



25 POSITION

0.598

UNITS = inch

\* TYP.

SUGGESTED SIZE MAY NOT BE SUITABLE FOR ALL APPLICATIONS

> DO NOT SCALE FROM DRAWING DRAWN: DATE: THESE DRAWINGS AND SPECIFICATIONS ARE 9-4-08 PAM JENKINS THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION SCALE: SHEET OF REV NorComp NTS 2 3 10 DWG NO. 772-EYY-213RYY1

