

Leitz iLAM Office A3 Laminator



Contemporary and compact, the Leitz iLAM Office laminating machine seamlessly integrates style and efficiency. This A3 laminator offers effortless lamination, featuring a fast 1-minute warm-up time and the ability to laminate an 80-micron A4 sheet in just 36 seconds, ensuring quick and easy document protection. The intuitive touch panel provides three pouch thickness settings for versatile use, along with an anti-jam reverse button for smooth removal of misfed pouches. The innovative SMART status LED uses lights and sounds: red during warm-up, green with an audible signal when ready, and flashing red for auto shut-off after 15 minutes of inactivity. Additionally, the SMART entry guide LEDs ensure perfect pouch alignment to prevent jams. Grey and white colour.

Attributes

- Ready to use in just 1 minute with an ultra quick warm-up time.
- Laminates an 80-micron A4 document in approximately 36 seconds, and is also compatible with A4 high-speed pouches for enhanced productivity.
- SMART status LED: glows red during warm-up and turns green with an acoustic signal when the laminator is ready to use.
- SMART entry guide LEDs: ensure pouches feed straight through the laminator to prevent jams.
- The intuitive touch panel features an anti-jam reverse button for easy removal of misfed pouches.
- Compatible with pouches ranging from 75 to 125 microns.
- Reduce energy consumption with the 15-minute auto shut-off feature. Sensors automatically detect inactivity and power down the machine to save energy.
- Includes a starter kit of 5x A4 pouches (80 microns).
- CE certified, TUV/GS
- Recommended for use with Leitz UDT Pouches.

Specifications

Number	72531084
Colour	dark grey
Dimensions (W x H x D)	470 x 102 x 144 mm
Laminating Speed (mm/min)	500
Temperature	126C-143C
Power Supply	220-240V AC 50/60Hz
Warm up Time (min)	1
Heating System	2 from outside heated rollers
Operation Mode	2 roller, no carrier, temperature controlled
Max. Laminating Width (mm)	330
Max. Laminating Thickness (mm)	0.5
Max. Pouch Thickness (microns)	75-125
Power Consumption (W)	1400
Dimensions (with Tray) mm	470,00x102,00x144,00 mm
Anti-Jam Technology	Manual reverse button
Approx. lamination time (A4)	36 secs (A4 80 micron)
Photo friendly	yes
Weight	2350 g
Pallet quantity	72
EAN code	4002432112913