



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Cable length	1.48 m
Depth	28.8 cm
Height	22.3 cm
Net weight	9.3 kg
Width	14.5 cm

Output

Rated power in W	1600 W
Maximum configurable power in W	1600 W
Crest factor	3 : 1

Conformance

Product certifications	CE
Standards	IEC 62040-1-1 IEC 62040-1-2

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Ambient air temperature for storage	-20...50 °C
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	4 h

Battery voltage	12 V
-----------------	------

Communications & Management

Free slots	1
------------	---

Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

Packing Units

Unit Type of Package 1	PCE
------------------------	-----

Number of Units in Package 1	1
------------------------------	---

Package 1 Weight	10.433 kg
------------------	-----------

Package 1 Height	32.995 cm
------------------	-----------

Package 1 width	23.495 cm
-----------------	-----------

Package 1 Length	36.5 cm
------------------	---------

Contractual warranty

Warranty	2 years
----------	---------
