

**1-95-566**

STANLEY® 750mm Forged Axial Bolt Cropper

**STANLEY®**

**3253561955662**



**Product Description :**

The STANLEY® Forged Handle Bolt Croppers have a choice between two types of blades: axial or flush cut. Comfortable ergonomic grips with guards, resistant to solvents. Drop forged chrome molybdenum steel jaws for durability and strength. Efficient and minimum effort cutting up to a maximum of 160Kg/mm<sup>2</sup> at Ø 10mm. Excentric screws for quick and easy adjusting of the blades.

**Product Features and Benefits :**

- STANLEY® 750 mm Forged Axial Bolt Cropper with drop forged chrome molybdenum steel jaws for durability and strength
- FORGED HANDLES: For strong cutting
- AXIAL OR FLUSH CUT: Choice between two types of blades.
- EFFICIENT AND MINIMUM EFFORT: Cutting up to a maximum of 160Kg/mm<sup>2</sup> at Ø 10mm
- ECCENTRIC SCREWS: Quick and easy blade adjustment
- COMFORTABLE ERGONOMIC GRIPS WITH GUARDS: Resistant to solvents
- YELLOW BODY FINISH AND PHOSPHATE JAWS: Very good visibility on worksite.

**Product Warranty :**

1 Year Warranty

**Technical specifications :**

- Max. Cutting Capacity [Metric] : 10 mm
- Max. Cutting Capacity [Imperial] : 0.47 in

1-95-566

STANLEY® 750mm Forged Axial Bolt Cropper



3253561955662

Product from the series 1-95-564

Ref	Titre
1-95-564	STANLEY® 450mm Forged Axial Bolt Cropper
1-95-566	STANLEY® 750mm Forged Axial Bolt Cropper
1-95-567	STANLEY® 36 in. (900mm) Forged Handle Bolt Cropper