


Battery Tools

ProSet® PB2500 & ProSet® PB3400

High speed cordless power tools with great strength and endurance

Lightweight and powerful tools with excellent ergonomics, great strength and great added features. Ensures high productivity and improves your return on investment with very low installation cost.


- **Durable** brushless motor that requires minimal maintenance
- **Long lasting** battery capable of placing an average of 1,200 ø4.8 mm standard blind rivets (PB2500, 2.0Ah) respectively 1,000 ø6,4 mm structural blind rivets (PB3400, 4.0Ah) per charge
- **Time saving** continuous operation in production environments without “tool overload”
- **Easy to use:**
 - Tool free, quick release nose housing and jaw guide removal and installation
 - All nose pieces for the POP Avdel rivets range include a rivet holding mechanism to allow the use of the tool in any direction - even upside down
 - Quick slide battery installation; Push button for easy removal of the battery from the tool
- **Warranty Europe:** 2 years in total (1 year & 1 year extension with online registration)



Rivet holding mechanism



Integral mandrel collector



Easy nose housing removal



Robust tool case for outdoor installation



PB3400 with quick release removable mandrel collector

Specifications ProSet® PB2500

Dimensions L x H	320 mm x 240 mm
Battery	DEWALT 18V Li-Ion 2.0Ah
Charger	DEWALT DCB115, with progress lamp display, 30 min. charge time (2.0 Ah)
Stroke	25 mm
Pulling force	8,500 N
Noise level	74 dB(A)
Capacity	Standard rivets ø 2.4 - 4.8 mm
Weight	1.69 kg including battery

Specifications ProSet® PB3400

Dimensions L x H	336 mm x 255 mm (2.0 Ah) 336 mm x 275 mm (4.0 Ah)
Battery	DEWALT 18V XR Li-Ion 2.0Ah or DEWALT 18V XR Li-Ion 4.0Ah
Charger	DEWALT DCB115, with progress lamp display, 30 min. charge time (2.0 Ah)
Stroke	30 mm
Pulling force	18,000 N
Noise level	77 dB(A)
Capacity	Blind rivets ø 4.8 - 6.4 mm
Weight	2.10 kg including 2.0 Ah battery 2.42 kg including 4.0 Ah battery