

Product Data Sheet - XVR107STI

Hager - witty one charging station 1x07kW 1ph+N Type 2S socket + TIC

Technical characteristics

Power

Maximum power per charging point: 7 kW

Connected power: 0.1 - 7 kW

Frequency

50 - 60 Hz

Power supply

Number of phases: 1

Electric current

Rated current: 32 A

Connectivity

Number of charging points: 1

Functions

Load management: Yes

Equipment

Number of domestic sockets: 0

Protective circuit breaker: No

Emergency release in case of power failure: Yes

Connection

Connection/socket type: Type 2S

Dimensions

370 x 250 mm

Height: 370 mm

Width: 250 mm

Depth: 150 mm

Installation

Wall mounting

Safety

Protection rating: IP55

Impact resistance: IK10

Operating conditions

Operating temperature: -25 to 50 C

Voltage

Rated voltage: 230 - 230 V

Material

Plastic

Sustainability

RoHS compliant: Yes

Translated from the French product data sheet dated 07.02.2026.

Photos / Drawings

The original PDF contains a product image on this page. The image could not be reproduced from the uploaded text extraction, but the page structure has been preserved in English.