

## Housing units UCT208 (Series UCT)

cast iron housing, radial insert ball bearing with grub screws in inner ring, RSR seals, for linear motion

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system ([https://www.schaeffler.de/content.schaeffler.de/en/news\\_media/index.jsp](https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp)) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
L	144 mm
H	114 mm
A	49 mm
A <sub>1</sub>	16 mm Tolerance: +0,2/0
A <sub>2</sub>	33 mm
B	49,2 mm
H <sub>1</sub>	102 mm Tolerance: 0/-0,5
L <sub>1</sub>	88 mm
L <sub>2</sub>	16 mm
L <sub>3</sub>	83 mm
N	29 mm

N <sub>1</sub>	19 mm	
N <sub>2</sub>	49 mm	
S <sub>1</sub>	30,2 mm	
T	83 mm	
m	2,32 kg	Mass
	T208	Designation, housing
	UC208	Designation, radial insert ball bearing



