

braking resistor - 72 ohm - 100 W - cable 3 m - IP65

VW3A7605R30

EAN Code: 3389119207225

Main

Range of product	Lexium
	Altivar
Range compatibility	Lexium 32i
	Lexium 32
	Lexium 05
	Lexium 15
	Lexium 52
	Altivar Machine ATV320
	Altivar 32
	Easy Lexium 16
Product compatibility	ATV32HU11M2
	ATV32HU15M2
	Variable speed drive ATV320 at 1.1 kW, 200240 V, single phase
	Variable speed drive ATV320 at 1.5 kW, 200240 V, single phase
	Motion servo drive LXM16D at 0.1 kW, 200230 V, single phase
	Motion servo drive LXM16D at 0.2 kW, 200230 V, single phase
	Motion servo drive LXM16D at 0.4 kW, 200230 V, single phase
	Motion servo drive LXM16D at 0.75 kW, 200230 V, single phase
	Motion servo drive LXM16D at 1 kW, 200230 V, single phase
	Motion servo drive LXM16D at 1.5 kW, 200230 V, single phase
Product or component type	Braking resistor
Ohmic value	72 Ohm

Complementary

Energy peak	2300 J at 480 V 2500 J at 400 V 3700 J at 230 V 5500 J at 115 V		
Average power available	25 W at 50 °C		
Continuous power	100 W		
Protection type	Thermal protection via the servo drive		
Net weight	0.85 kg		
Cable length	3 m		

Environment

IP degree of protection	IP65
Ambient air temperature for storage	-2585 °C
Ambient air temperature for operation	050 °C

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1	1		
Package 1 Height	4.5 cm		
Package 1 Width	40.0 cm		
Package 1 Length	13.0 cm		
Package 1 Weight	840.0 a		

Logistical informations

Country of origin CZ

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

⊗ Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration

Use Again


○ Repack and remanufacture		
Take-back	No	

VW3A7605R30

Dimensions Drawings

Braking Resistor

Dimensions



Dimensions in mm

b	b1	С	c1	Н
145	110	15	15.5	98

Dimensions in in.

b	b1	С	c1	Н
5.70	4.33	0.59	0.61	3.85