

370044161

Stainless steel industrial enclosure IGSN A2 380 x 380 x 167 mm

Stainless steel industrial enclosure IGSN A2 380 x 380 x 167 mm

Drawing 3D Data

Technical data

Height	380 mm
Width	380 mm
Depth	167 mm
Material	Stainless Steel
Material quality	1.4301/304
Ingress protection	IP66
Degree of protection norm	EN 60529
Impact strength	IK09
temperature min.	-60 °C
temperature max.	175 °C
Seal material	VMQ-(silicone)
Flame spread, sideways	HL 3
Rate of head dispersion	HL 3
Smoke gas concentration	HL 3
Other versions on request	EMV
Approvals	LR (Lloyd's Register), UL (508A)

Commercial data

Country of origin	IN
Order unit	1 Piece
Customs tarif number	85369095
Weight	6.37 kg
GTIN	4057624608507


ETIM classification

ETIM 8	EC000058


ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany

Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de


Accessories



100110450
Mounting plate 37383816/37004416/21




100614390
DIN rail 35/7,5 for 37.383816



100620240
Earth rail for 37.383816



100681240
Protective conductor busbar for 34.40xxx /xx.0044xx



370100040
Flange size 4 - 130x360x3



371050000
Stainless steel external mounting brackets



379900010
Mounting set for Stainless-steel enclosures