

PEN-TYPE LED TORCH IN ALUMINIUM - 170 LUMEN

889 TM



- Anodised Aluminium body
- Built-in front glass
- 3 lighting modes: high-medium-strobe
- Hanging clip
- Switch on with back button

Light source	1 x SMD LED
Autonomy min-max (hours)	1,5-3
Battery type (not supplied)	2 x AA
Protection level	IP54
Light beam distance (m)	80
Working temperature (°C)	-20 ÷ 50
Color temperature (k)	6500
Light flux (lm)	170-55-Strobo
N° lighting modes	3

Family details

Code	LxPxH mm	Weight gr	Quantity for packaging
U08890071	152x24x24	64	1

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000

Sets / Compositons

Articles



5003/150M - Assortment with pliers, hammers, and chisels (15 pcs.)

Stanley Black & Decker Italia S.r.l.

Sede legale: Via Energy Park 6 - 20871 Vimercate (MB)
Sede operativa: Via Volta 3 - 21020 Monvalle (VA) Italia
Partita IVA e C.F.: 03225990138

StanleyBlack&Decker

Società a Socio Unico soggetta a coord. e controllo
da parte di Stanley Black & Decker, Inc.
Capitale Sociale I.V. € 12.000.000