

## EPK85-60KC

**Battery operated cutting tool 60 kN with scissor head, 85 mm capacity.**

Scissor type cut offering easy access.  
Ergonomic handle and triggers to allow its manoeuvrability with gloves.  
Tool perfectly balanced to ensure a maximum comfort.

<b>F</b> kN	<b>Ø</b> mm	<b>mm</b>	<b>kg</b>
60	85	520 x 435 x 83	6.5



### Characteristics:

- **Ergonomic design:** optimizing the position of centre of gravity.
- **Cutting capacity:** Cu and Al cables up to 85 mm diameter.
- **Head rotation:** 350°.
- **Data display:**
  - OLED technology
  - Cumulative working cycles
  - Battery status maintenance notification
  - Fault codes
- **Retraction:** automatic after cutting completion.
- **Mechanism:** two-stage hydraulic system with fast-feed and power-control.
- **Assistance:** LED to illuminate the cut area.
- **Maintenance:** please contact your nearest Sicame Group Service Center.
  - Replacement of cutting blades
  - Periodic maintenance: 20 000 cycles.
- **Kit content:**
  - Battery operated tool
  - 2 batteries 18 V, 5,0 Ah
  - 1 Fast charger
  - Thermoplastic carrying case (dimensions: 585 x 498 x 135 mm)
  - Total kit weight: 12,5 kg



EPK85-60KC



BL1850B



CLM1890HC