



PRODUCT DATASHEET

Datasheet creation date: 2025/07/08 5:13 (UTC)



6200VV

Single-Row Deep Groove Ball Bearings

Parts Number

6200VVC3

Boundary Dimensions

d	10	mm	Bore diameter
D	30	mm	Outside diameter
B	9	mm	Width
r (min.)	0.6	mm	Chamfer dimension

Basic Load Ratings

Cr	5600	N	Basic dynamic load rating
C0r	2390	N	Basic static load rating

Speeds

Grease	28000	min-1	Grease lubrication
--------	-------	-------	--------------------

Abutment and Fillet Dimensions

da (min.)	14	mm	Diameter of shaft abutment
da (max.)	16	mm	Diameter of shaft abutment
Da (max.)	26	mm	Diameter of housing abutment
ra (max.)	0.6	mm	Radius of shaft or housing fillet
Dx (min.)	0	mm	Diameter of snap ring recess in the housing
Cy (max.)	0	mm	Distance from outer ring side face to snap ring back face

Calculation factors

fo	13.2	Factor
----	------	--------

Additional information

z	8	Number of Balls
Dw	4.762	mm Ball Diameter

Mass

Mass approx.	0.032	kg	Mass approx.
--------------	-------	----	--------------

