

Illumination element, 24 V

46-580.1F21

Distribution by
Rs-online



<https://rs-online.eao.com/component/46-580.1F...>

Your product:



46-580.1F21

Illumination element, 24 V

MOUNTING

Mounting type: Panel mounting

OPERATING-/INDICATION PART

Illumination colour: Orange

ELECTRICAL CHARACTERISTICS

Operating voltage: 24 V AC/DC -20% / +10%

Protection class: II, according to EN / IEC 61140

MECHANICAL CHARACTERISTICS

Weight: 0.147 kg

AMBIENT CONDITION

IP front protection: IP44

IK front protection: IK07

Operating temperature: – 25 °C ... + 65 °C

CERTIFICATE

Conformities: CE

Standards: EN 55015, EN 61000-3-2, EN 61000-3-3, EN 61547, IEC EN 60947-1, IEC EN 60947-5-1, IEC EN 62471

OTHER

Short Description:	Illumination element, 24 V, Ø 75 mm x 75 mm, Panel mounting, 24 V AC/DC -20% / +10%
Titel Accessory:	Illumination element, 24 V
Dimension:	Ø 75 mm x 75 mm
Housing material:	Plastic
Product attributes:	For Signal Light Tower