



---

**PRODUCT-DETAILS**

# SPLHCB20/25M

## 20MM GS-TPR COND SS BRD 25M-BL



---

**General Information**

<b>Extended Product Type:</b>	SPLHCB20/25M
<b>Product ID:</b>	7TCA296100R0170
<b>EAN:</b>	5020963011955
<b>Catalog Description:</b>	20MM GS-TPR COND SS BRD 25M-BL
<b>Long Description:</b>	Liquid Tight, Extreme Temperature Covered Steel Flexible Conduit with Stainless Steel Overbraid, Medium Flexibility, Nominal Conduit Size 20mm, Outside Diameter 21.1mm, Inside Diameter 15.9mm, Static Bend Radius 80mm, Reel Length 25 Meters, Thermoplastic Rubber Cover with Galvanised Steel Core, Black
<b>Display Name:</b>	SPLHCB20/25M

---

**Additional Information**

<b>Product Main Type:</b>	Adaptaflex Flexible Cable Protection
<b>Application:</b>	Liquid Tight - Extreme Temperature Environments

---

**Ordering**

---

EAN:	5020963011955
UPC:	786210245508

---

## Dimensions

---

Outside Diameter:	21.1 mm
-------------------	---------

---

## Technical

---

Number of Batteries:	0
Color:	Black
Material:	Galvanized Steel Core with Thermoplastic Rubber Cover

---

## Environmental

---

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

## Container Information

---

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5020963011955
Package Level 1 Height:	8 in 203 mm
Package Level 1 Depth / Length:	16 in 406 mm
Package Level 1 Width:	16 in 406 mm

---

## Certificates and Declarations

---

Declaration of Conformity - CE:	9AKK107492A9618
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

---

## External Classifications and Standards

---

ETIM 8:	EC001179 - Protective metallic hose
ETIM 9:	EC001179 - Protective metallic hose
UNSPSC:	39131706

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

