

C-152646

3rd ANGLE (AMERICAN) PROJECTION

DIMENSIONS IN INCHES. DO NOT SCALE PRINT
DIMENSIONS THUS [] IN MM.

INSULATION COLOUR BROWN.

.031 TONGUE THICKNESS.
[0.79]

.281 DIA.
[7.14]

FOR
INSULATION DIA.

.035 - .075
[0.89 1.90]

SERRATIONS

.031 MIN.
[0.79]

.242 MIN.
[6.15]

.640 MAX.
[16.26]

.787 MAX.
[19.99]

.171±.003 DIA.
[4.34±.08]

FOR #8 STUD.

ENGINEERING
OFFICE
MASTER

FR 152646

E .242 DIM. REPOSITIONED DR 19/11/77				AIRCRAFT-MARINE PRODUCTS (GREAT BRITAIN) LTD 19		CUSTOMER COPY REFERENCE ONLY			
D .787, .242 ± .055 / .075 WMS DR 26/11/77				MATERIAL AND FINISH		AMP industrial A DIVISION OF AIRCRAFT-MARINE PRODUCTS (GREAT BRITAIN) LTD. STANMORE, MIDDLESEX			
C PICTORIAL CHANGE ONLY AWVC 5-4-72				COPPER - ANNEALED.		CLASS STRATOTHERM P.I.D.G.			
B CHANGED PICTORIALY PCH 25-4-72				NICKEL PLATED		TYPE RING TONGUE			
A .035/.085 WMS .040/100 DR 22/11/77				WIRE - RANGE - INSULATION 24-22		TOLERANCE EXCEPT AS NOTED ± .015 [0.38] ± 1° V			
LTR REVISION RECORD DR CRK DATE				SCALE 6:1		LOC NO		REV	
DR DE WELLS 27/10/69				NAME		E A C-152646		E	
CHK LWD 27.10.69 APP Ughind 25.2.70				WIRE TERMINAL ASSY.					