



— PRODUCT DATA SHEET

TAC6R



TAC6R

PRODUCT DESCRIPTION

Easy to use, robust and reliable: With the TAC6R, you are ready for your next mission. The extremely compact tactical flashlight has everything you need for a search or security mission, hunting or prepping—a no-nonsense tactical End Cap Switch for intuitive, rapid control as well as a strong battery and hard-anodized aluminium housing. Thanks to our groundbreaking Multi-Lens Technology, you can even choose between a multi-mission tactical beam combining flood and spotlight or choose to use either one individually.



- Multi-mission tactical beam: Choose between a light pattern designed for tactical operations with a combined flood and spotlight and individual flood or spotlight (Multi-Lens Technology)
- Intuitive, rapid control: Tactical End Cap Switch and mechanical transport lock
- Rugged & action-ready: Hard-anodized aluminium housing as well as high water and dust resistance (IP68)
- Light functions: Check, TAC Mid, TAC High, Search, TAC Boost, Strobe; with up to 2000 lm (34,000 cd)
- Powerful 18650 Li-Ion battery, rechargeable via USB-C

TECHNICAL DATA	
Weight incl. batteries [g]	158
Material	Aluminum alloy
Length [mm]	139
Tube diameter [mm]	25
Head diameter [mm]	35
POWER SUPPLY	
Battery quantity	1
Rechargeable	Yes
Battery type	Lithium-ion
Total battery voltage [V]	3.6
Total battery capacity [mAh]	2600
Total battery energy [Wh]	19.36 Wh
Battery replaceable	Yes
Charging time [min]	180
Energy status indicator	Battery Indicator, Charge Indicator, Low Battery Warning
FURTHER SPECIFICATIONS	
IP class	IP68
Drop test (drop height) [m]	2
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS					
TAC Boost, Check, TAC Mid, TAC High, Search					
LIGHT SOURCE		MAIN			
Amount LEDs		3			
Color		Cool White			
Color temperature [K]		6000 to 7500			
Color rendering index (CRI)		70			
LIGHT VALUES					
	TAC Boost	Check	TAC Mid	TAC High	Search
Light output [lm]	2000	100	600	1100	500
Beam distance [m]	370	20	200	280	270
Run time [h]	-	15	3.5	2	3
SWITCH					
End-cap Multifunctional switch					
TECHNOLOGIES & FEATRUES					
Multi-Mission, Tactical Beam, Intuitive, Rapid Control, Rugged & Action-Ready, IP68, Sustainable, Flicker Free, Transportation Lock, Backup Mode, USB-C Charging					

TAC6R

PACKAGING AND LOGISTICS



PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	1 set of rechargeable batteries (18650), Pouch Type G, Adjustable hand strap
Item No.	503052
Color	Black
Customs tariff number	85131000
STERLING RRP inc / ex vat	£119.95/ £99.96
EURO RRP inc / ex vat	€119.95 / €97.52

SINGLE PACKAGE

Dimensions W x H x D [cm]	7.2 x 21 x 6.3
Gross weight [g]	350
GTIN-13	4058205035965

EXPORT CARTON

Unit	16
Dimensions W x H x D [cm]	44.5 x 17.5 x 31
Gross weight [g]	6230
GTIN-13	4058205035941

TAC6R

ACCESSORIES

PRODUCT CATEGORY	ITEM NO.	PRODUCT NAME
Bags & Holsters	503193	Tactical Professional Holster Type D
Mounts & Brackets	0362	Universal Mounting System
Mounts & Brackets	503188	Picatinny Rail Mount A
Color filters & Signal caps	502237	Signal Cone 35.1mm
Color filters & Signal caps	502238	Color Filter Set 35.1mm
Bags & Holsters	0342	Pouch Type G
Remote Controls	503194	Remote Switch Type H
Roll Protection	503191	Finger Ring A
Mounts & Brackets	503189	Recoil Ring A

TAC6R

PRODUCT SERIES

Tactical Brilliance: With our TAC-series, nothing is left to chance. Whether you depend on tactical light at your job as a member of the police, special forces or security company or need additional light when hunting or prepping in your free time—when light matters, our TAC-series flashlights have your back.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.

*) 7 year warranty only if registered, otherwise 2 years. Warranty conditions viewable at <https://ledlenser.com/en/infos-service/warranty/>

1) Measured values according to ANSI/PLATO FL 1 in the respective setting named. If no setting is specifically named, the luminous flux (lumens/lm) and range (meters/m) values refer to the brightest setting and the burn time

(hours/h) values refer to the lowest setting. A boost function (if available) can be used several times, but is only available for a short time at a time. In case the lamp is equipped with colored LED(s), the measured values are given with white light or the white LED. If the lamp has different energy modes, the "energy saving mode" is the basis for the measurement.

2) Calculated value of the capacity in watt-hours (Wh). This applies to the battery(ies) contained in the delivery condition of the respective item or, in the case of lamps with rechargeable battery, to the battery(ies) contained herein in a fully charged condition.

9) All aluminium components are made of at least 75 % recycled aluminium and may thus vary in surface structure and color.