



15590-231 Over Trousers

windproof

MASCOT® SAFE SUPREME



100% polyester

210 g/m²



Ripstop. The product is according to EN ISO 20471 certified to retain its qualities with 50 domestic washes. Hydrostatic pressure test > 10,000 mmH₂O according to EN ISO 811.

Industrial care category B3

Certifications



- Breathable, wind and waterproof with taped seams.
- Light fabric lining.
- Elastic and drawstring waist.
- Adjustable kneepad pockets so kneepads can be optimally placed on the knee.
- Extra long zip with storm flap on outside of lower leg so they can be easily pulled on over boots.
- Press stud adjustment at foot.
- Co-certified for use with MASCOT kneepad type SHORT or LONG, as the kneepad pocket is height-adjustable.



EN ISO20471



HIGH-VIS GROUP:



EN343



Logo

The product is certified with maximum 0,5600m² logo area. This approved area must not be exceeded. Logo on, respectively, front or back of the product can constitute only a maximum of 50% of the total approved logo area in order to maintain the EN ISO 20471-certification. Note: The listed area is only a guide to how much space is available for logo placement. In order to maintain the product's hi-vis class according to EN ISO 20471, the instructions on logo size must be observed.

Logo placement:

- Workwear logo. Left back pocket. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Right back pocket. Max 10x5 cm/3.9x1.9 inches
- Workwear logo. Vertical on left thigh, read from the bottom upwards. Max 25x5 cm/9.8x1.9 inches
- Workwear logo. Horizontal on left thigh. Max 11x5 cm/4.3x1.9 inches
- Workwear logo. Vertical on right thigh, read from the top downwards. Max 25x5 cm/9.8x1.9 inches
- Workwear logo. Horizontal on right thigh. Max 11x5 cm/4.3x1.9 inches
- Workwear logo. Special placement. Contact to discuss further

Technical info

Fluorescent and with oblique, transverse reflective strips. Breathable, wind and waterproof. Taped seams. Light lining. Elastic and drawstring at waist. Belt loops. D-ring. Front pockets with flap and press stud fastening. Reinforced ruler pocket. Adjustable kneepad pockets. Zip with storm flap on outside of legs. Press stud adjustment at foot. We recommend 00418-100, 00718-100, 50454-916 & 20118-915 kneepads for this model. Co-certified together with kneepad type SHORT or LONG in accordance with EN 14404.

User

